

PRODUCTS

- Hand Tools
- Holemaking
- Bending
- Fishing
- Cable Pulling
- Wire & Cable Termination
- Voice Data Video
- Testing & Measurement
- Storage & Material Handling
- Hydraulic Pumps & Miscellaneous

 Search by Keyword/Cat.No./UPC No.

 |< << >> >| Page 1/2

	Name	UPC	Catalog #
	Draw Stud-3/4" x 2-1/8"	04040	249AVBB
	Replacement Draw Stud 3/4in. x 2-1/8in.	04040	249AVBB
	3/4" x 2-1/8" Draw Stud	04040	249AVBB
	Conduit & Pipe: 3/4", Hole Size: 1.115 Inch, 28.3 (mm), Capacity Mild Steel: 10 GA, 3.5 mm, Replacement Punch 123AV 04008 , Replacement Die 124AV 06972 , Replacement Draw Stud 249AVBB 04040	22564	72BB
	Conduit & Pipe: , Hole Size: 1.280 Inch, 32.5 (mm), Capacity Mild Steel: 10 GA, 3.5 mm, Replacement Punch 24459, Replacement Die 35168 , Replacement Draw Stud 249AVBB 04040	24476	24476
	Conduit & Pipe: 1", Hole Size: 1.362 Inch, 34.6 (mm), Capacity Mild Steel: 10 GA, 3.5 mm, Replacement Punch 125AV 04010 , Replacement Die 126AV 04011 , Replacement Draw Stud 249AVBB 04040	22565	73BB
	Conduit & Pipe: , Hole Size: 1.457 Inch, 37.0 (mm), Capacity Mild Steel: 10 GA, 3.5 mm,, Replacement Punch 18331 18331 , Replacement Die 32008 32008 , Replacement Draw Stud 249AVBB 04040	18890	730EBB-37
	Conduit & Pipe: , Hole Size: 1.595 Inch, 40.5 (mm), Capacity Mild Steel: 10 GA, 3.5 mm, Replacement Punch 24462, Replacement Die 35159 , Replacement Draw Stud 249AVBB 04040	24477	24477
	Conduit & Pipe: 1-1/4 , Hole Size: 1-11/16 1.701 Inch, 43.2 (mm), Capacity Mild Steel: 10 GA, 3.5 mm, Replacement Punch 127AV 06974 , Replacement Die 128AV 04013 , Replacement Draw Stud 249AVBB 04040	22566	74BB
	Replacement Part for 7361SB/34359 Cabinet 3/48#039; (19.0 mm) x 2-1/88#039; (54 mm) Drive Screw	04040	249AVBB

 |< << >> >| Page 1/2