



Select a Language

SEARCH

[Supplier Center](#) [Distributor Center](#)

BROWSE PRODUCTS

Category: Browse by Brand:

PRODUCTS

- [Bending](#)
- [Bolt Cutters](#)
- [Cable Termination](#)
- [CATV/Broadband Instruments](#)
- [Connectors](#)
- [Electric Test Instruments](#)
- [Fasteners](#)
- [Fiber Connections](#)
- [Fiber Optic Instruments](#)
- [Fishing](#)
- [Hydraulic Tools](#)
- [Knockout Sets](#)
- [Material Handling](#)
- [Network Instruments](#)
- [Power Tool Accessories](#)
- [Professional Hand Tools](#)
- [Pulling](#)
- [Safety Products](#)
- [Storage](#)
- [Telco Instruments](#)
- [VDV Instruments](#)
- [VDV Termination](#)
- [VDV Tools](#)
- [Wire Termination](#)

[VDV Tools](#) > [VDV Crimpers](#) > [VDV Crimpers Die Sets](#) > DIE 22-14 AWG OPEN BARREL BLISTER

DIE 22-14 AWG OPEN BARREL BLISTER

[Images](#)



[SAVE PRODUCT TO PDF](#)

Related Products



User Reviews

[\(No Reviews Yet.\)](#)

Cat No: **PA2096** UPC No: **769328104400**

[Request Product Info or Demo ▶](#)

[Where to Buy ▶](#)

- [Description](#)
- [Specifications](#)
- [Reviews](#)

- Application : For Open Barrel, Box And Terminal Systems
- Cable Type : Open Barrel Non-Insulated Terminals, Wide Lugs And Power Contacts
- Connection : Solid Or Stranded Wire, 22 - 14 AWG (0.340 - 2.500 SQ-MM), F Type
- Crimp Size : 16-14/22-18 AWG (1.500 - 2.500/0.340 - 0.750 SQ-MM)
- Package : Blister
- Sub Brand : CrimpALL®
- Type : Interchangeable

0

[About Us](#) | [Manuals](#) | [News & Events](#) | [Contact Us](#) | [Careers](#) | [Submit an Idea](#) | [Promotions](#) | [Support](#)

[CA Transparency in Supply Chains Act](#) | [Environmental Responsibility](#) | [Privacy Policy](#) | [Terms of Use](#) | [Textron](#) | [Site Map](#)
[Rothenberger](#) | [Sherman & Reilly](#) | [HD Electric](#) | [Klauke](#) | [Greenlee Communications](#)