



Specialty Tools & Instruments

[Company Info](#) [Contact Us](#) [Policies](#) [Distributors](#)

Hello, Guest [Call Toll FREE 800-697-8665](#)
Shopping Cart:

SEARCH

[Hand Tools](#) [Instruments](#) [New Products](#) [Manuals](#) [Media Resources](#) [Distributor List](#)

[ACCOUNT LOGIN](#)



Home > Instruments



DCiS1 - iBorescope WiFi Enabled Real Time Video Capture
 Item Id: DCiS1
 The DCiS1 is perfect for WiFi-enabled real-time video capture

Availability: Purchase through our Certified Internet Retailers

Email a friend

Share |



- [Product Description](#)
- [Video](#)
- [Related Products](#)
- [Key Features](#)
- [Additional Videos](#)
- [Specifications](#)

- [\[product_feature_name\]](#)

Average Rating [totalrating] [review_link]



[short_review]

[long_review]

Reviewed by: [user_name] from [user_city]. [user_email] on [review_date]

Compatible with	iPad, iPad 2, "iPad 3", iPhone 3GS, iPhone 4, iPhone 4S, iPhone 5, iPod Touch (3rd, 4th, 5th Generation) running iOS4.1 or later; any device running Android 2.2 or higher
Security	WiFi (WEP) password
Video Resolution	640 x 480 pixels (VGA)
Frame Rate	30 frames per second (fps)
Streaming Video Format	MPEG4
WiFi Range	60 ft. (18m), max (unobstructed)
Camera Lighting	2 white LEDs
Camera Head Diameter	0.39 in. (9.8mm)
Camera Depth of Field	½ in. to 12 in. (12.7 to 305mm)
Probe Length	6' ft. (1.83m)
Probe Minimum Bending Radius	1.77 in. (45mm)
Dust & Water Resistance Rating (Probe & Camera Head only)	IP67
Operating Voltage	3.7V internal from 5V input

Current Consumption	600 mA, max @ 5VDC
Operating Temperature	32° to 104°F (0° to 40°C)
Power Supply	Rechargeable Li-ion battery with 5V/1A output
Life of Full Battery Charge	3 hours, typical



LIVE Support
OFFLINE

Mailing List
Subscribe to our Newsletter

go


Subscribe

Unsubscribe

enter email



Click to Download
2014Tool Catalog



Click To Download
2014 Instrument Catalog

[Terms and Conditions](#) |
 [Become an Affiliate](#) |
 [Product Index](#) |
 [Category Index](#) |
 [About Us](#) |
 [FAQ's](#) |
 [Shipping Policy](#) |
 [Locate A Dealer](#)

[Home](#) |
 [Company](#) |
 [Hand Tools](#) |
 [Test Instruments](#) |
 [Newsroom](#) |
 [New Products](#) |
 [Clearance](#) |
 [Contact Us](#) |
 [Search](#) |
 [Site Map](#)

[Plumbing Tools](#) |
 [Woodworking Tools](#) |
 [Specialty Tools](#) |
 [Machinist Tools](#) |
 [Measuring Tools](#)

Headquartered in New York City for 90 years, *General Tools & Instruments LLC* is the leader in specialty hand tools and instruments.
Copyright 2014 General Tools & Instruments LLC- All Rights Reserved.

ABOUT SSL CERTIFICATES