

Twist-Lock® Devices

20 Ampere, 125, 250 Volts and 277 Volts AC

2 Pole, 3 Wire Grounding

Insulgrip® Connector Bodies and Receptacles



20A 125V
NEMA L5-20R
UL/CSA
1 HP



20A 250V
NEMA L6-20R
UL/CSA
2 HP



20A 277V AC
NEMA L7-20R
UL/CSA
2 HP

Connector Bodies

Watertight Safety-Shroud®		IP66 SUITABILITY		
Description	Cord Dia.	Catalog Numbers		
Black Valox® housing, white Valox® clamps.	.360"-.930" (9-24)	HBL2313SW	HBL2323SW	HBL2333SW

Insulgrip		IP20 SUITABILITY		
Description	Cord Dia.	Catalog Numbers		
Black and white nylon.	.360"-.930" (9-24)	HBL2313	HBL2323	HBL2333
Corrosion resistant, yellow nylon.	.360"-.930" (9-24)	HBL23CM13	HBL23CM23	-
All black nylon.	.360"-.930" (9-24)	HBL2313BK	HBL2323BK	-
Cord clamps with removable inserts. All black nylon.	.360"-.930" (9-24)	HBL2313EBK	HBL2323EBK	-

Accessories on page B-51.

Valise®		IP20 SUITABILITY		
Description	Cord Dia.	Catalog Numbers		
Yellow nylon.	.325"-.720" (8.26-18.3)	HBL2313VY	HBL2323VY	-
Black nylon.	.325"-.720" (8.26-18.3)	HBL2313VBK	HBL2323VBK	HBL2333VBK

Accessories on page B-51.

Receptacles

Watertight Safety-Shroud, Back Wired		IP66 SUITABILITY		
Description	Catalog Numbers			
Gray Valox® housing and flange.	HBL2310SW HBL2320SW HBL2330SW			

Accessories on page B-54.

Safety-Shroud Twist-Lock, Back Wired		IP20 SUITABILITY		
Description	Catalog Numbers			
Gray Valox® angle housing, one gang.	HBL2310AR HBL2320AR HBL2330AR			
Gray Valox® surface mounting, one gang.	HBL2310SR HBL2320SR HBL2330SR			
Gray Valox® semi-flush, two gang.	HBL2310SR2 HBL2320SR2 HBL2330SR2			

Accessories on page B-54.


Single Flush, Back and Side Wired		IP20 SUITABILITY		
Description	Catalog Numbers			
Black nylon face.	HBL2310 HBL2320 HBL2330			
Isolated ground, orange nylon face.	IG2310 IG2320 -			
Corrosion resistant, yellow nylon face.	HBL23CM10 - -			
Ring terminal connection.	HBL2310RT HBL2320RT -			

Accessories on page B-50.


Insulgrip Flanged Receptacles

Description	Catalog Numbers		
Nylon casing, back wired.	HBL2316	HBL2326	HBL2336


Accessories on page B-50.



HBL2316



HBL2310



HBL2320SR2




HBL2320SR




HBL2323SW



HBL2313



HBL2313VY



HBL2320SW



HBL2320AR

Valox® is a trademark of SABIC Innovative Plastics, acquired from General Electric Company.

