



POWER CONNECTIONS



Twist-Lock® Full Line Catalog Section 'B'

2-Pole/3-Wire Connector Bodies

Amps	Voltage	Cat. No.
15	125V	HBL4729C
20	125V	HBL2313
20	250V	HBL2323



Plugs

Amps	Voltage	Cat. No.
15	125V	HBL4720C
20	125V	HBL2311
20	250V	HBL2321



Receptacles

Amps	Voltage	Cat. No.
15	125V	HBL4700*
20	125V	HBL2310
20	250V	HBL2320



* Duplex

Isolated Ground Receptacles

Amps	Voltage	Cat. No.
15	125V	IG4700A*
20	125V	IG2310
20	250V	IG2320



* Duplex

3 Pole/4 Wire Connector Bodies

Amps	Voltage	Cat. No.
20	3Ø480V	HBL2433
30	3Ø480V	HBL2733



Plugs

Amps	Voltage	Cat. No.
20	3Ø480V	HBL2431
30	3Ø480V	HBL2731



Receptacles

Amps	Voltage	Cat. No.
20	3Ø480	HBL2430
30	3Ø480	HBL2730



Single Pole Plugs Full Line Catalog Section 'F'

Male Plugs

Amps	Color	Cat. No.
400A	Black	HBL400PTBK
400A	White	HBL400PTW
400A	Red	HBL400PTR
400A	Blue	HBL400PTBL
400A	Green	HBL400PTGN



Female Plugs

Amps	Color	Cat. No.
400A	Black	HBL400CTBK
400A	White	HBL400CTW
400A	Red	HBL400CTR
400A	Blue	HBL400CTBL
400A	Green	HBL400CTGN



Pin and Sleeve Full Line Catalog Section 'E'

Connector Bodies

Amps	Poles/ Wires	Voltage	Cat. No.
30	3P/4W	3Ø480	HBL430C7W
30	3P/4W	3Ø250	HBL430C9W
30	3P/4W	125/250	HBL430C12W
60	3P/4W	3Ø480	HBL460C7W
60	3P/4W	3Ø250	HBL460C9W
60	3P/4W	125/250	HBL460C12W



Plugs

Amps	Poles/ Wires	Voltage	Cat. No.
30	3P/4W	3Ø480	HBL430P7W
30	3P/4W	3Ø250	HBL430P9W
30	3P/4W	125/250	HBL430P12W
60	3P/4W	3Ø480	HBL460P7W
60	3P/4W	3Ø250	HBL460P9W
60	3P/4W	125/250	HBL460P12W



Receptacles

Amps	Poles/ Wires	Voltage	Cat. No.
30	3P/4W	3Ø480	HBL430R7W
30	3P/4W	3Ø250	HBL430R9W
30	3P/4W	125/250	HBL430R12W
60	3P/4W	3Ø480	HBL460R7W
60	3P/4W	3Ø250	HBL460R9W
60	3P/4W	125/250	HBL460R12W



Single Pole Receptacles & Accessories Full Line Catalog Section 'F'

400 Amp, Panel Mount Receptacles

Color	Male Cat. No.	Female Cat. No.
Black	HBLSITBK	HBLSRTBK
White	HBLSITW	HBLSRTW
Red	HBLSITR	HBLSRTR
Blue	HBLSITBL	HBLSRTBL
Green	HBLSITGN	HBLSRTGN



Accessories

Description	Cat. No.
Tapping T	HBLTBK
Tri-Tap Connector	HBL3TAP
Distribution Block	HBL7DB



Straight Blade Devices Full Line Catalog Section 'A'

2 Pole/3 Wire Connector Body, 15A/125V

Cat. No.	Cat. No.
HBL5269C	

Plugs, 15A/125V

Body Type	Cat. No.
Straight	HBL5266C
Angled 90°	HBL5266CA



Industrial Duplex Receptacles, Nylon Back and Side Wired

Color	15A/125V Cat. No.	20A/125V Cat. No.
Brown	HBL5262	HBL5362
Ivory	HBL5262I	HBL5362I
Gray	HBL5262GY	HBL5362GY
Red	HBL5262R	HBL5362R
White	HBL5262W	HBL5362W
Black	HBL5262BK	HBL5362BK



Compact Industrial Duplex Receptacles

Color	15A/125V Cat. No.	20A/125V Cat. No.
Brown	HBL5252	HBL5352
Ivory	HBL5252I	HBL5352I
Gray	HBL5252GY	HBL5352GY
Red	HBL5252R	HBL5352R
White	HBL5252W	HBL5352W
Black	HBL5252BK	HBL5352BK
Blue	-	HBL5352BL



Hospital Grade Duplex Receptacles, Tamper Resistant

Color	15A/125V Cat. No.	20A/125V Cat. No.
Brown	HBL8200SGA	HBL8300SGA
Ivory	HBL8200SGIA	HBL8300SGIA
Gray	HBL8200SGGYA	HBL8300SGGYA
Red	HBL8200SGRA	HBL8300SGRA
White	HBL8200SGWA	HBL8300SGWA

4-PLEX® Receptacles

Color	15A/125V Cat. No.	20A/125V Cat. No.
Brown	HBL415	HBL420
Ivory	HBL415I	HBL420I
Gray	HBL415GY	HBL420GY
White	HBL415W	HBL420W
Black	HBL415BK	HBL420BK



4-PLEX® Adapter Plates

Color	Cat. No.
Brown	HBL4AP
Ivory	HBL4API
Gray	HBL4APGY
White	HBL4APW



© Hubbell Wiring Device-Kellems
Hubbell Incorporated (Delaware)
1-203-882-4800
www.hubbell-wiring.com

www.hubbell-solutions.com/edu

Wall Switches

Full Line Catalog Section 'C'

20 Amp/120-277V AC

Pole/Way	Cat. No.
Single Pole	HBL1221
Double Pole	HBL1222
3-Way	HBL1223
4-Way	HBL1224



Above products have brown toggle.
For alternate toggle colors, add suffix of GY(gray), I(ivory), W (white), R (red).

20 Amp/120-277V AC Pilot Light (light on with load on)

Pole/Way	Cat. No.
Single Pole	HBL1221PL
Double Pole	HBL1222PL
3-Way	HBL1223PL



20 Amp/120-277V AC Illuminated (light on with load off)

Pole/ Toggle Way	Color	Cat. No.
Single	Ivory	HBL1221IL
Single	Clear	HBL1221ILC
Three	Ivory	HBL1223IL
Three	Clear	HBL1223ILC



20 Amp/120-277V AC 3-Position (center off)

Type	Cat. No.
SPDT Momentary	HBL1557
SPDT Maintained	HBL1385
DPDT Maintained	HBL1386



Unfused Disconnect Switches

Full Line Catalog Section 'C'

Circuit-Lock® Switches

Amps	Cat. No.
30A	HBLDS3
60A	HBLDS6
100A	HBLDS10



Circuit-Lock® Switches with Aux. Contact

Amps	Cat. No.
30A	HBLDS3AC
60A	HBLDS6AC
100A	HBLDS10AC

Fused Disconnect Switches

Full Line Catalog Section 'C'

Circuit-Lock Safety Enclosure

Amps	Cat. No.
30A	FDS30
60A	FDS60



Lock Switches

Full Line Catalog Section 'C'

Key Lock Switches & Plate

Pole/Way	Cat. No.
Single	HBL1221RKL
Double	HBL1222RKL
Three	HBL1223RKL
Four	HBL1224RKL
1-Gang SS Plate	S12RKL



20 Amp/120-277V AC

Pole/Way	Cat. No.
Single-Pole	HBL1221L
Double-Pole	HBL1222L
3-Way	HBL1223L
4-Way	HBL1224L



20 Amp/120-277V AC 3-Position (center off)

Type	Cat. No.
SPDT Momentary	HBL1557L
DPDT Maintained	HBL1386L

20 Amp/120-277V AC, Double Pole, Double Throw

Cat. No.	Cat. No.
HBL1386L	



Wall Plates

Full Line Catalog Section 'K'

Toggle Switch Plates, Plastic


Gang	Switches	Cat No.
1	One	P1
2	Two	P2
3	Three	P3



Above products are Ivory. For alternate toggle colors, add suffix of G(gray), X (brown), W (white), R (red).

Duplex Receptacle Plates

Gang	Material	Cat. No.
1	Ivory Plastic	P8
1	Stainless Steel	S8
2	Ivory Plastic	P82
2	Stainless Steel	S82



Manual Motor Controllers

Full Line Catalog Section 'C'

Switches, 600V AC

Amps	Poles	Cat. No.
30	Double	HBL7832BW
30	Three	HBL7810BW
60	Three	HBL7863



Enclosures

Use with HBL Switch	Enclosure Type/material	Cat. No.
7810BW	Type 1 non-metallic	HBL1389BW
7810BW	Type 1 metal	HBL1379BW
7810BW	Type 3R metal	HBL13R89BW
7863FW	Type 3R metal	HBL16R93



Style Line® Devices

Full Line Catalog Sections 'A' & 'C'

Receptacles

Color	15 Amp Cat. No.	20 Amp Cat. No.
Brown	HBL2152	HBL2162
Ivory	HBL2152I	HBL2162I
Gray	HBL2152GY	HBL2162GY
White	HBL2152WA	HBL2162WA



Single Pole Switches

Color	15 Amp Cat. No.	20 Amp Cat. No.
Brown	HBL2101	HBL2121
Ivory	HBL2101I	HBL2121I
Gray	HBL2101GY	HBL2121GY
White	HBL2101WA	HBL2121WA



Double Pole Switches, 20 Amp

Color	Cat. No.
Brown	HBL2122
Ivory	HBL2122I
Gray	HBL2122GY
White	HBL2122WA

3-Way Switches

Color	15 Amp Cat. No.	20 Amp Cat. No.
Brown	HBL2103	HBL2123
Ivory	HBL2103I	HBL2123I
Gray	HBL2103GY	HBL2123GY
White	HBL2103WA	HBL2123WA

4-Way Switches, 20 Amp

Color	Cat. No.
Brown	HBL2124
Ivory	HBL2124I
Gray	HBL2124GY
White	HBL2124WA

Weatherproof Plates

Full Line Catalog Section 'K'

Duplex or StyleLine® Opening, Non-Metallic Polycarbonate, Single Gang

Orientation	Cat. No.
Vertical	WP826MP
Horizontal	WP826MHP



H5143LC 03/04



Hubbell Wiring Device-Kellems
Hubbell Incorporated (Delaware)
1-203-882-4800
www.hubbell-wiring.com

www.hubbell-solutions.com/edu