

## Marine Products

# Switches & Weatherproof Switch Plates

15 and 20 Ampere, 120-277 Volt



### Commercial Series

Description	Catalog Numbers
Single-pole toggle switch for controlling AC load from one point, brown handle. See note A.	CS115*
Same as #CS115 except gray handle. See note A.	CS115GY*
Same as #CS115 except ivory handle. See note A.	CS115I
Same as #CS115 except office white handle. See note A.	CS115OW*
Same as #CS115 except white handle. See note A.	CS115W*
Three-way toggle switch for controlling AC load from two points, brown handle. See note A.	CS315*
Same as #CS315 except gray handle. See note A.	CS315GY*
Same as #CS315 except ivory handle. See note A.	CS315I*
Same as #CS315 except office white handle. See note A.	CS315OW*
Same as #CS315 except white handle. See note A.	CS315W*



CS115I

### Special Application Series

Description	Catalog Numbers
20A 120V toggle switch with neon lamp set in ivory handle. Handle illuminates when switch is in "OFF" position.	HBL1221IL
20A 120V three-way toggle switch with illuminated ivory handle for controlling AC load from two points. Handle illuminates when "OFF."	HBL1223IL*
20A 120V single-pole toggle switch with neon lamp set in clear red handle. Handle illuminates when switch is "ON." Serves as instant reminder that current is flowing to an appliance.	HBL1221PL
20A 120V three-way toggle switch for controlling AC load from two points. Red handle illuminates when "ON."	HBL1223PL*
Single-pole PresSwitch® for controlling AC load from one point. Switch activated brown button.	HBL1281
Same as #HBL1281 except ivory button.	HBL1281I*
Three-way PresSwitch® for controlling AC load from two points. Switch activated brown button.	HBL1283†
Same as #HBL1283 except ivory button.	HBL1283I††
Yellow neoprene weatherproof plate for use only with PresSwitches. PresSwitch button is activated when bubble is pressed. <b>Not CSA.</b>	HBL17CM50†
Clear silicone rubber weatherproof bubble plate for use with all AC toggle switches and PresSwitches. Also ideal for use with lighted handle toggle switches. <b>Not CSA.</b>	HBL1795



HBL1221IL



HBL1221PL



HBL1281



HBL1283



HBL17CM50



HBL1795

### Outlet Box

Description	Catalog Numbers
Plastic switch/receptacle box. Measures 3 7/32" x 2 3/16" x 2 1/2" (83.3 x 55.6 x 63.5) deep. For mounting in walls without studs. A support strap is provided which pulls box tightly against back side of wall. <b>Not CSA.</b>	HBL6079

Note: Will accept locking fork terminal to comply with ABYC standards.

\*Not shown.

†Not UL Listed.



HBL6079

