

Marine Products

Marine Grade Lift Cover Plates



Marine Grade Weatherproof Plates

Description	Catalog Numbers
Yellow Valox® spring-loaded lift cover plate for weatherproofing duplex receptacles. Stainless steel screws and neoprene gasket included for mounting to FS/FD type weatherproof boxes. IP20 SUITABILITY.	HBL52CM21
Same as #HBL52CM21 except white in color. IP20 SUITABILITY.	HBL52CM21W
Same as #HBL52CM21 except gray in color. IP20 SUITABILITY.	HBL5221*
Same as #HBL52CM21 except for mounting to standard boxes. IP20 SUITABILITY.	HBL52CM22*
Same as #HBL52CM22 except gray in color. IP20 SUITABILITY.	HBL5222*
Yellow Valox® spring-loaded lift cover plate for weatherproofing single straight blade receptacles. Stainless steel screws and neoprene gasket included. For mounting to FS/FD type weatherproof boxes. IP44 SUITABILITY.	HBL74CM23WO
Same as #HBL74CM23WO except gray in color. IP44 SUITABILITY.	HBL7423WO*
Yellow Valox® spring-loaded lift cover plate for weatherproofing old style #26CM10 receptacle. Meets the most stringent requirements of UL's three listing categories for weatherproof plates. Stainless steel screws and neoprene gasket included for mounting to FS/FD type weatherproof boxes. IP44 SUITABILITY.	HBL74CM24WO
Same as #HBL74CM24WO except gray in color. IP44 SUITABILITY.	HBL7424WO*
Yellow Valox® spring-loaded lift cover plate for weatherproofing #HBL26CM10 receptacle. Meets the most stringent requirements of UL's three listing categories for weatherproof plates. Stainless steel screws and neoprene gasket included for mounting to FS/FD type weatherproof boxes. IP44 SUITABILITY.	HBL74CM25WOA
Same as #HBL74CM25WOA except white in color. IP44 SUITABILITY.	HBL74CM25WOAW
Same as #HBL74CM25WOA except gray in color. IP44 SUITABILITY.	HBL7425WOA*
Yellow Valox® lift cover plate for weatherproofing 50A receptacles. Meets requirements of the most stringent of UL's three listing categories for weatherproof plates. Stainless steel screws and a neoprene gasket included. For mounting to FS/FD type weatherproof boxes. IP44 SUITABILITY.	HBL77CM74WO
Same as #HBL77CM74WO except gray in color. IP44 SUITABILITY.	HBL7774WO*

Note: *Not shown.

Commercial Grade Weatherproof Plates

Available in a host of configurations – Twist-Lock® and straight blade receptacles in single or duplex as well as switches – these plates are perfect for marine use. The PVC resists deterioration over time and has high tensile and impact strength. Each plate comes with a tightly sealing, rubberized gasket and a super strong lift cover spring.

Commercial Grade Weatherproof Plates

Description	Catalog Numbers
Gray PVC weatherproof lift cover plate for toggle switches (such as #CS115). For vertical mounting in standard or FS/FD type boxes.	CWP1CR
Gray PVC weatherproof lift cover plate for duplex receptacles (such as #HBL52CM62). For vertical mounting in standard or FS/FD type boxes.	CWP8CR
Gray PVC weatherproof lift cover plate for ground fault receptacles (such as #GF5252MGYA) and Style Line® receptacles. For vertical mounting in standard or FS/FD type boxes.	CWP26CR

Note: Valox® is a registered trademark of General Electric Company.



HBL52CM21



HBL74CM23WO
HBL74CM24WO
HBL74CM25WOA



HBL77CM74WO



CWP1CR



CWP8CR



CWP26CR