



Metal PlugTrak® - 3 Ft. Base and Cover

Boxes and Fittings

Catalog Number		Amp	Circuits	# Single Receptacles	Receptacle Spacing (in.)
Ivory	Gray				
HBL20GB306IV	HBL20GB306GY	15	Single	6	6
HBL20IG306IV	HBL20IG306GY	15	IG/Single	6	6
HBL24GB306IV	HBL24GB306GY	20	Single	6	6

Description	Color	Catalog Number
One-Gang Device Box	Ivory	HBL2048IV
	Gray	HBL2048GY
Two-Gang Device Box	Ivory	HBL20482IV
	Gray	HBL20482GY

Metal PlugTrak® - 5 Ft. Base and Cover

Catalog Number		Amp	Circuits	# Single Receptacles	Receptacle Spacing (in.)
Ivory	Gray				
HBL20GB506IV	HBL20GB506GY	15	Single	10	6
HBL20GB512IV	HBL20GB512GY	15	Single	5	12
HBL20GBA512IV	HBL20GBA512GY	15	Two	5	12
HBL20IG512IV	HBL20IG512GY	15	IG/Single	5	12
HBL24GB506IV	HBL24GB506GY	20	Single	10	6
HBL24GB512IV	HBL24GB512GY	20	Single	5	12
HBL24GBA512IV	HBL24GBA512GY	20	Two	5	12

Internal Corner Coupling	Galv. Steel	HBL2017TC
External Elbow	Ivory	HBL2018CIV
	Gray	HBL2018CGY
Flat Elbow	Ivory	HBL2011IV
	Gray	HBL2011GY
Tee	Ivory	HBL2015IV
	Gray	HBL2015GY

Metal PlugTrak® - 6 Ft. Base and Cover

Catalog Number		Amp	Circuits	# Single Receptacles	Receptacle Spacing (in.)
Ivory	Gray				
HBL20GB606IV	HBL20GB606GY	15	Single	12	6
HBL20GB609IV	HBL20GB609GY	15	Single	8	9
HBL20GB612IV	HBL20GB612GY	15	Single	6	12
HBL20GB618IV	HBL20GB618GY	15	Single	4	18
HBL20GBA609IV	HBL20GBA609GY	15	Two	8	9
HBL20GBA612IV	HBL20GBA612GY	15	Two	6	12
HBL20GBA618IV	HBL20GBA618GY	15	Two	4	18
HBL20IG606IV	HBL20IG606GY	15	IG/Single	12	6
HBL24GB606IV	HBL24GB606GY	20	Single	12	6
HBL24GB612IV	HBL24GB612GY	20	Single	6	12
HBL24GB618IV	HBL24GB618GY	20	Single	4	18
HBL24GBA612IV	HBL24GBA612GY	20	Two	6	12
HBL24GBA618IV	HBL24GBA618GY	20	Two	4	18

Entrance End Fitting	Ivory	HBL2010A2IV
	Gray	HBL2010A2GY
Large Entrance End Fitting	Ivory	HBL2010A3IV
	Gray	HBL2010A3GY
Blank End Fitting	Ivory	HBL2010BIV
	Gray	HBL2010BGY
Cover Clip	Ivory	HBL2006IV
	Gray	HBL2006GY
Supporting Clip	Galv. Steel	HBL2003SC
Coupling	Galv. Steel	HBL2001C

For detailed descriptions, photos and dimensions see pages 14-16.

Portable Metal PlugTrak®

Catalog Number		Length	Cord Length	Amp	Circuits	# Single Receptacles
Ivory	Gray					
HBL20C215IV	HBL20C215GY	40 In.	6 Ft.	15	Single	6
HBL20C315IV	HBL20C315GY	64 In.	6 Ft.	15	Single	8

Notes: Hubbell Metal PlugTrak is supplied with two **HBL2010B(IV)** or **(GY)** Blank End Fittings and one **HBL2001C**.

"IV" suffix to catalog number for ivory finish. "GY" suffix to catalog number for gray finish.

Outlets match raceway color. "IG" Isolated receptacles are orange color.