

IDEC - PUSHBUTTONS & PILOT LIGHTS - YW SERIES



Features:

- » Small and light weight construction
- » Locking lever removable contact block assembly
- » Fingersafe IP20 contacts as standard
- » Up to 3 contact blocks possible for non-illuminated pushbuttons



YW1B-M1E10G



YW1L-M2E10Q4A



YW1L-M2E11QS-K



YW-E10

Features:

- » Small and light weight construction
- » Fingersafe IP20 contacts as standard
- » Super bright LEDs - very low heat and long life
- » Incandescent - low cost option with long life



YW1P-2EQ0G



YW1P-2EQ4R



YW1P-2EM42A

YW SERIES - DIA 22mm IP65 (COMPLETE UNITS)

Type	Operation	Contact	Colour	Part No.
Flush	Momentary	1 NO	Black	YW1B-M1E10B
		1 NO	Green	YW1B-M1E10G
		1 NO	Yellow	YW1B-M1E10Y
		1 NC	Red	YW1B-M1E01R
Mushroom 40mm	Momentary	1 NC	Red	YW1B-M4E01R

Illuminated Pushbuttons (Lamp included) - 24VAC/DC

Extended LED	Momentary	1NO	Amber	YW1L-M2E10Q4A
		1NO	Green	YW1L-M2E10Q4G
		1NO	White	YW1L-M2E10Q4W
		1NO	Yellow	YW1L-M2E10Q4Y
		1NC	Red	YW1L-M2E01Q4R
Extended Incandescent	Momentary	1NO	Amber	YW1L-M2E10Q7A
		1NO	Green	YW1L-M2E10Q7G
		1NO	White	YW1L-M2E10Q7W
		1NO	Yellow	YW1L-M2E10Q7Y
		1NC	Red	YW1L-M2E01Q7R

Illuminated Pushbuttons (LED included) - 240VAC

Extended LED	Momentary	1NO-1NC	Amber	YW1L-M2E11QA-K
		1NO-1NC	Green	YW1L-M2E11QG-K
		1NO-1NC	Red	YW1L-M2E11QR-K
		1NO-1NC	Blue	YW1L-M2E11QS-K
		1NO-1NC	White	YW1L-M2E11QW-K
		1NO-1NC	Yellow	YW1L-M2E11QY-K

Contact Blocks

Contact Block 1NO	YW-E10
Contact Block 1NC	YW-E01

YW SERIES - DIA 22mm IP65 (COMPLETE UNITS)

Type	Operating Voltage	Part No.
Full Voltage (Lamp Not Included)		
Without Lamp		YW1P-2EQ0*

Note: Lamps to be ordered separately. See table on next page.

Full Voltage (24V AC/DC LED Included)

Amber	24V AC/DC	YW1P-2EQ4A
Green	24V AC/DC	YW1P-2EQ4G
Red	24V AC/DC	YW1P-2EQ4R
Blue	24V AC/DC	YW1P-2EQ4S

Transformer Type (Lamp Included)

LED	100/110VAC	YW1P-2EH2*
	230/240VAC	YW1P-2EM42*

Note: LED Lamp type LSTD-6 included (6V)

Incandescent	100/110VAC	YW1P-2EH5*
	230/240VAC	YW1P-2EM45*

Note: Incandescent Lamp IS-6 included (6V)

* Colour: A - (Amber), G - (Green), R - (Red), S - (Blue), W - (White), Y - (Yellow)