

3-1618391-7 Product Details

 [Share](#)
 [Print](#)
 [Email](#)


3-1618391-7

TE Internal Number: 3-1618391-7

 [Active](#)

Contactors

 [Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Contactor Type = Sealed
- LEV100 Series
- DC Actuating System
- 1 Poles
- Contact Arrangement = 1 Form X, SPST-NO-DM

[View all Features](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

 [Add to My Part List](#)
 [Request Sample](#)
 [Find Similar Products](#)
 [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- None Available

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Contactor Type = Sealed
- Series = LEV100
- Terminal Configuration = 2 x M4 Bolt

Electrical Characteristics:

- [Actuating System](#) = DC
- Contact Rating = 100A
- [Coil - Rated Voltage \(VDC\)](#) = 48
- [Coil Voltage, Max. \(VDC\)](#) = 52

Termination Features:

- Coil Termination = Wire

Body Features:

- Torque = 30-40 in-lbs
- Mount Type = Bottom Mount

Contact Features:

- [Number of Poles](#) = 1

Configuration Features:

- [Contact Arrangement](#) = 1 Form X, SPST-NO-DM
- Auxiliary Switch Contact Arrangement = None
- Coil Wire Length (mm [in]) = 381 [15]

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Packaging Features:

- Packaging Method = Individual

Other:

- Brand = Kilovac

Corporate Information

[Who We Are](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)

Quick Links

[Check Distributor Inventory](#)
[Cross Reference](#)
[Find Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Search Knowledge Base](#)
[Manage your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address 

