



TE CONNECTIVITY (TE)
KCS03X024EAAA=CONTACTOR, CURRENT SENSE

Kilovac
KCS03X024EAAA
TE Internal Number: 1618408-5

- EU RoHS Compliant
- EU ELV Compliant
- Contact Arrangement: **1 Form X, SPST-NO DM**
- Wire Size (AWG) **22**
- Contact Current Rating (A) **600**
- Coil Voltage (Max) (VDC) **28**
- Coil Resistance (Ω) **126**
- [See All Features](#)

- Active
- [PRODUCT DRAWING](#)
English
- [3D PDF](#)
- [See All Documentation](#)

North America ▼

DISTRIBUTOR	QUANTITY	DATE AS OF
MOUSER ELECTRONICS (800) 346-6873	26	2017/06/05
MASTER ELECTRONICS CORP. 1-888-473-5297	25	2017/06/06
DIGI-KEY ELECTRONICS 1-800-344-4539	23	2017/06/06

[View More \(1\)](#)

[SAVE TO LIST](#) ▼

[FIND SIMILAR PRODUCTS](#)

[DOCUMENTATION](#) [FEATURES](#) [PRODUCT COMPLIANCE](#)

Please review product documents or [contact us](#) for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.

Product Type Features	Terminal Configuration	M8 x 1.25 Stud
	Contactor Type	Sealed
	Product Category	Electromechanical Relays
	Model	KCS Series
	Product Type	Contactor
	Product Classification	Relays - Contactors
	Arc Cover	Without
Electrical Characteristics	Coil Voltage (Max) (VDC)	28
	Coil Resistance (Ω)	126
	Coil Voltage Rating (VDC)	18 – 28
	Contact Switching Voltage (Max) (VDC)	600
	Actuating System	DC
Contact Features	Contact Arrangement	1 Form X, SPST-NO DM

About TE Connectivity For Partners Customer Support **CALL US** **LIVE CHAT** United States

<ul style="list-style-type: none"> Our Company Events TE News Center Careers Investors Corporate Responsibility Terms and Conditions of Sale 	<ul style="list-style-type: none"> Distributors Suppliers 	<ul style="list-style-type: none"> Email or Call Us Find Authorized Distributors What's New on TE.com Product FAQs Share Feedback 	<ul style="list-style-type: none"> Select Country & Language United States (EN) Germany (DE) China (中文) Japan (日本語) Find Your Country ▼
---	---	--	---

Packaging Features	Packaging Method	Individual
Other	Torque (in-lbs)	11 NM

Compatible Products [Contact Product Support](#)

