

5 - 1618388 - 5 Product Details

[Share](#)
[Print](#)
[Email](#)



5 - 1618388 - 5

TE Internal Number: 5 - 1618388 - 5

 [Active](#)

Contactors


[Always EU RoHS/ELV Compliant](#) ([Statement of Compliance](#))

Product Highlights:

- ? Contactor Type = Sealed
- ? LEV200 Series
- ? DC Actuating System
- ? 1 Poles
- ? Contact Arrangement = 1 Form X, SPST -NO-DM

[View all Features](#)

 [Add to My Part List](#)

 [Request Sample](#)

 [Find Similar Products](#)

 [Buy Product](#)

Quick Links

- ? [Check Pricing & Availability](#)
- ? [Search for Tooling](#)
- ? [Product Feature Selector](#)
- ? [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

? None Available

Catalog Pages/Data Sheets:

? None Available

Product Specifications:

? None Available

Application Specifications:

? None Available

Instruction Sheets:

? None Available

CAD Files:

? None Available

Additional Information:

? [Product Line Information](#)

Related Products:

? [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- ? Contactor Type = Sealed
- ? Series = LEV200
- ? Terminal Configuration = 10 -32 Stud

Electrical Characteristics:

- ? [Actuating System](#) = DC
- ? Contact Rating = 500A
- ? [Coil - Rated Voltage \(VDC\)](#) = 24
- ? [Coil Voltage, Max. \(VDC\)](#) = 24

Termination Features:

? Coil Termination = Wire

Body Features:

- ? Torque = 80 -100 in -lbs
- ? Mount Type = Bottom Mount

Contact Features:

? [Number of Poles](#) = 1

Configuration Features:

- ? [Contact Arrangement](#) = 1 Form X, SPST -NO-DM
- ? Auxiliary Switch Contact Arrangement = None
- ? Coil Wire Length (mm [in]) = 390 [15.3]

Industry Standards:

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Not relevant for lead free process
- ? RoHS/ELV Compliance History = Always was RoHS compliant

Packaging Features:

? Packaging Method = Individual

Other:

? Brand = Kilovac

Corporate Information

[Who We Are](#)

[Investors](#)

[News Room](#)

[Supplier Portal](#)

[Careers](#)

Quick Links

[Check Distributor Inventory](#)

[Cross Reference](#)

[Find Documents & Drawings](#)

[Product Compliance Support Center](#)

[Site Map](#)

Customer Support

[Email or Chat With Us](#)

[Find a Phone Number](#)

[Search Knowledge Base](#)

[Manage your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

