

Ratcheting Crimper, 10-22 AWG - Insulated Terminals

3005CR



(0)
Write a review




- Crimps insulated terminals onto 10-22 AWG stranded copper wire
- Adjustable compound action design puts more crimping power into each squeeze
- Three crimping cavities in one tool: 22-16 AWG (Red), 16-14 AWG (Blue) and 12-10 AWG (Yellow) terminals
- Built-in ratchet ensures full-cycle crimping for a uniform crimp every time
- Unique cavity design provides consistent crimp from either side of the tool
- Dial adjusts the amount of force applied to the crimp
- Dual-material molded grips provide added comfort

[BUY ONLINE](#)

[FIND LOCAL RETAILER](#)



VIDEO



DOWNLOADS

- [Brochure](#)
- [Instructions](#)

IMAGES

- JPG (High Resolution):** [3005cr_photo.jpg](#)
- PNG (Transparent Background):** [3005cr.png](#)

INTERACTIVE CATALOG

- [Product Page](#)
- [Product Section](#)

The full-cycle Ratcheting Crimper crimps 10-22 AWG insulated wire terminals. This tool features three crimping cavities in one tool with color-coded wire markings for three size ranges of insulated terminals. Crimper design provides low effort to crimp while maintaining a high terminal pull-off force. Built-in ratchet ensures full-cycle crimping for a uniform crimp every time. Compound lever-action of narrow-span handles puts more crimping power into each squeeze. Comfort grips help reduce hand fatigue.

Specifications

Type: Ratcheting Crimper

Connector Type: Insulated

Application: Wire Crimping

Overall Length: 9" (2.3 cm)

Special Features: 3 Crimping Cavities

Overall Height: 0.09" (0.2 cm)

Material: Steel

Overall Width: 3" (7.6 cm)

Handle Color: Red and Black

Weight: 1.3 lb (0.6 kg)

Cable Size: 10-22 AWG Stranded

UPC: 092644344008

Additional Information

WARRANTY

WARNINGS

- Always wear approved eye protection.
- NOT insulated. Plastic-dipped or slip-on plastic handles are NOT intended for protection against electrical shock.

RELATED ITEMS



55475
Tradesman Pro™
Tool Bag Backpack,
35 Pockets, Black,
17.5-Inch

★★★★★ 0.0 (0)



60135
Tradesman Pro™
Standard Kneeling
Pad

★★★★★ 0.0 (0)



J1005
Journeyman™
Crimping and
Cutting Tool

★★★★★ 0.0 (0)



T1710
Compound Action
Ratcheting Crimper
- Insulated
Terminals

★★★★★ 0.0 (0)



T1715
Full Cycle
Ratcheting Crimper
- Insulated
Terminals

★★★★★ 0.0 (0)

Reviews



Be the first to review this product

CUSTOMER SERVICE

1-800-553-4676

