

T-5mm Single Level, Long Protrusion(SSF-LXH100XX-01 Series)

INDEX

PRODUCT TREE



- [Product Table](#)
- [Applications / Uses](#)
- [Features / Options](#)
- [Order Samples](#)
- [Stock/Price Request](#)
- [Sales and Tech Support](#)

1. [Product Gallery](#)
2. [eLeds.com](#)
3. [PCB Indicator](#)
4. [Dome PCB Indicator](#)
5. [5mm Dome PCB Indicators](#)
6. [T-5mm Single Level, Long Protrusion\(SSF-LXH100XX-01 Series\)](#)

SPEC! Image next to part no. indicates cad file.

Lumex drawings are in PDF format. If you don't have Adobe Acrobat, click on this icon to

[download a free copy](#)



Lumex Part Number	BRIGHTNESS	Dice Material	Emitted Color	Peak (nm)	Epoxy Lens	Operating Current (mA)	Operating TYP, Vf (V)	Brightness TYP, mcd	Brightness @ mA	View Angle 2x THETA
SSF-LXH100GD-01 SPEC!	STANDARD	GaP	Green ■	565	Green D Dfsd	5-25	2.1	8	20	60
SSF-LXH100ID-01 SPEC!	STANDARD	GaAsP	High Intensity Red ■	635	Red D Dfsd	5-25	2.1	8	20	60
SSF-LXH100SID-01 SPEC!	HIGH	AlInGaP	Super High Intensity Red ■	636	Red D Dfsd	5-25	2.0	80	20	60
SSF-LXH100SOD-01 SPEC!	HIGH	AlInGaP	Sup Pure Green ■	610	Orange D Dfsd	5-25	2.0	80	20	60
SSF-LXH100SRD-01 SPEC!	STANDARD	GaAlAs	Sup Red ■	660	Red D Dfsd	5-25	1.8	40	20	60
SSF-LXH100SUGD-01 SPEC!	HIGH	AlInGaP	Sup Ultra Green ■	574	Green D Dfsd	5-25	2.2	30	20	60
SSF-LXH100SYD-01 SPEC!	HIGH	AlInGaP	Sup Yellow ■	590	Yellow D Dfsd	5-25	2.0	80	20	60
SSF-LXH100USB-01 SPEC!	HIGH	InGaN/SiC	Ultra Sup Blue ■	470	Blue D Dfsd	5-25	3.5	40	20	60
SSF-LXH100YD-01 SPEC!	STANDARD	GaAsP	Yellow ■	585	Yellow D Dfsd	5-25	2.1	80	20	60

Applications / Uses

[\[top of page\]](#)

- Board Level Status Indicators
- Board Level Fault Indicators
- Circuit Troubleshooting Indicators
- Warning/Alarm Lights
- Backlighting of Overlays
- Post Lighting Switches and Keypads

Features / Options

[\[top of page\]](#)

- State-of-the-Art, Chip Technology
- Easy Drop-In-Board Installation
- Right Angle to the Board Position
- Choice of Colors and Lens Finishes
- Low Current Versions Available
- Color or Intensity Sorting Available
- Blinking LED
- With Internal Resistor for 5V and 12V Operation
- Black or Gray Holders for high Contrast

[Home](#)

[What's
New](#)

[Product
Gallery](#)

[Product
Search](#)

[X-Ref Search
Engine](#)

[Tech
Notes](#)

[Sales and Tech
Support](#)

[Corporate
Info](#)

290 East Helen Road Palatine, IL 60067 Telephone: (847) 359-2790 Facsimile: (847) 359-8904 E-mail us at sales@lumex.com

© 1997-2001 Lumex, Inc.