


**Product Details for 052 -0204 -0001**



**052 -0204 -0001**

Tyco Part Number: 7 - 1532004 - 0

[Active](#)

**SMB RF Connectors**

[Not ELV or RoHS Compliant](#)

**Product Highlights:**

- ? Connector
- ? Plug
- ? Miniature
- ? Terminate To Coaxial Cable
- ? Coupler Style = Threaded

[View all Features](#)

**Quick Links**

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

**Documentation & Additional Information**

**Product Drawings:**

- ? [RIGHT ANGLE PLUG S -50 SERIES](#) (PDF, English)

**Catalog Pages/Data Sheets:**

- ? None Available

**Product Specifications:**

- ? None Available

**Application Specifications:**

- ? None Available

**Instruction Sheets:**

- ? [Right -Angle Plugs](#) (PDF, English)

**CAD Files:**

- ? None Available

**Additional Information:**

- ? [Product Line Information](#)

**Related Products:**

- ? [Tooling](#)

[List all Documents](#)

**Product Features** (Please use the Product Drawing for all design activity)

**Product Type Features:**

- ? [Product Type](#) = Connector
- ? [Gender](#) = Plug
- ? Connector Series = Miniature
- ? [Body Style](#) = Right Angle
- ? [Grade](#) = Commercial
- ? Safety Wire Holes = Without
- ? Thread Size = 4.83 [.190] -32 UNF -2B
- ? Body Material = Brass
- ? Coupling Nut Style = Hex
- ? Dielectric Material = TEFLON

**Mechanical Attachment:**

- ? [Panel Attachment](#) = Without

**Electrical Characteristics:**

- ? [Connector Impedance \(?\)](#) = 50
- ? Environmental Seal = Without
- ? Solderless = No

**Termination Related Features:**

- ? [Coaxial Cable Termination Type](#) = Solder

**Body Related Features:**

- ? Coupler Style = Threaded
- ? [Pin Protection](#) = Without
- ? Solder Lug = Without
- ? [Body Plating](#) = Silver
- ? Cable Jacket Diameter (mm [in]) = 2.34 [0.092]

**Contact Related Features:**

- ? [Center Contact Plating](#) = Gold
- ? Contacts = With

**Industry Standards:**

- ? [RoHS/ELV Compliance](#) = Not ELV/RoHS compliant
- ? [Lead Free Solder Processes](#) = Not suitable for lead free processing

**Conditions for Usage:**

- ? [Terminate To](#) = Coaxial Cable

**Other:**

- ? Brand = Microdot