

Quick Jump:


A cordless, butane powered hotmelt glue gun

- Completely portable, lets you work almost anywhere
- Power and durability to get the job done in industrial applications
- Runs continuously for up to 140 minutes on butane gas, easily refilled in 20 seconds
- Fast, easy start up with push button piezo ignition
- Operates up to 392° F.
- Reaches working temperature in just 3 to 4 minutes
- Fast, even adhesive flow with standard 1/2" (12 mm) diameter glue sticks
- 200 Watt heater delivers up to 1.9 lbs. of glue per hour
- Ergonomically designed for ease of use
- Safety lock on fuel flow control wheel prevents unintentional gas flow
- Instant glue flow cut-off reduces dripping
- Built-in folding stand and fuel level window
- Four interchangeable brass application nozzles available
- Optional glue sticks available for special applications
- Fuel not included
- Patented: USA, Taiwan, Germany, Japan & China



ORDERING INFORMATION

MODEL NO.	DESCRIPTION
GG-100	PortaPro™ Glue Gun
GG-100K	PortaPro™ Glue Gun Kit



35412 - 12 General Purpose glue sticks 12" long x 1/2" dia.
 35413 - 12 Carton Closing glue sticks 12" long x 1/2" dia.
 35414 - 12 Woodworking glue sticks 12" long x 1/2" dia.

OPTIONAL ACCESSORIES

[Click Here](#) for Glue Stick Specifications

ITEM NO.	DESCRIPTION
35408	Standard General Purpose Tip
35409	Needle Extension Tip
35410	Diagonal Cut Extension Tip
35411	Spreader Extension Tip
35412	General Purpose Glue Sticks — 12 sticks
35413	Carton Closing Glue Sticks — 12 sticks
35414	Woodworking Glue Sticks — 12 sticks
35454	General Purpose Glue Sticks — 20 lb carton (approx. 290 sticks)
35455	Carton Closing Glue Sticks — 20 lb carton (approx. 290 sticks)
35456	Woodworking Glue Sticks — 20 lb carton (approx. 290 sticks)

SPECIFICATIONS

■ Dimensions: 8.4" (L) x 2.1" (W) x 8.0" (H)	■ Weight: 14.8 oz. w/o gas
■ Recommended Fuel: Master Ultratane® Butane	■ Avg. Run Time: Approx. 140 minutes (full tank)
■ Operating Temp: Approx. 392° F	■ Glue Melt Rate: 1.9 lbs. per hour
■ Ramp Up Time: 3 - 4 minutes	■ Fuel Capacity: 20 ml.
■ Shipping Weight: GG -100/2 lbs., GG-100K/4 lbs.	

[Click here](#) for MSDS for Glue Sticks



ULTRATANE® BUTANE

Use Master Ultratane Butane for best performance. The only approved butane recommended to fuel all Master butane powered products.

Users should independently evaluate the suitability of the product for their application.

WARNING

The Department of Transportation Hazardous Material Regulations forbid carriage of butane or other flammable gas products on passenger aircraft. Do not pack this item or any other flammable gas item in any checked or carry-on baggage.

By-products of the combustion of the fuel used by this product contain chemicals known to the state of California to cause cancer and reproductive harm.