

Steel Fish Tape, 1/8-Inch x 50-Foot


56331

- Durable 1/8-Inch wide steel fish tapes are firm yet flexible for large wire pulls
- Optimized design of the tape housing decreases payout effort
- Slip-resistant housing geometry improves winding power
- Multi-position handle gives you a firm, steady grip as you pull tape from the case
- Descending laser etched markings in 1-Foot (0.3 m) increments
- Easy-to-read distance marks allow you to more accurately measure conduit runs and the amount of tape left to pay out
- Polypropylene case and handle offer high impact resistance
- U.S. Patents: 8164025; 8168921; 8212178; 9895773; 10099316




[BUY ONLINE](#)

[FIND LOCAL RETAILER](#)



VIDEO



DOWNLOADS

- [Brochure](#)
- [Instructions](#)

IMAGES

JPG (High Resolution): [56331_photo.jpg](#)

INTERACTIVE CATALOG

- [Product Page](#)
- [Product Section](#)

The Klein Tools' 50-Foot Steel Fish Tape is perfect for wire runs associated with light commercial, residential and voice-data-video installations. The optimized housing and handle design decreases payout effort and reduces binding. The large handle allows for a firm, steady grip as you pull the tape from the housing. The tape features laser-etched descending markings placed at every foot. These markings allow you to accurately measure the depth of conduit runs and determine the amount of tape left to pay out.

Specifications

| | | | |
|-------------------|--------------------------|------------|--|
| Type: | Steel Fish Tape | Color: | Orange/Black |
| Application: | Wire Pulling | Tape Size: | 50.0' x 0.125" x 0.045" (15.2 m x 0.3 cm x 0.1 cm) |
| Special Features: | Optimized Housing Design | Diameter: | 7" (17.8 cm) |
| Overall Length: | 1.20" (3.0 cm) | Tape End: | Double Loop |
| Overall Height: | 8.81" (22.4 cm) | Weight: | 1.5 lb (680.4g) |
| Overall Width: | 7.55" (19.2 cm) | UPC: | 092644563317 |
| Material: | Steel | | |

Additional Information

WARRANTY

WARNINGS

- Wear approved eye protection when feeding, pulling or rewinding fish tape.
- Do NOT use any fish tape on or near live circuits. Use extreme caution when working near any electrical equipment.
- Use a safe work position to avoid loss of balance when using fish tape.
- Never remove screws while fish tape is coiled inside reel.
- Never form pulling loop into a single loop (into shape of a fish hook) or create a sharp edge that could cause fish tape to catch on other objects or cut into insulation of surrounding wires. Pulling loop should only be formed into a double loop.

ACCESSORIES



40234
Journeyman Wire
Pulling Gloves, XL



51010
Premium Synthetic
Wax Cable Pulling
Lube 1-Quart



51028
Premium Synthetic
Clear Lubricant 1-
Quart



51100
Wire Pulling Foam
Lubricant



D2000-9NETP
Lineman's Pliers,
Fish Tape Pulling,
9-Inch

RELATED ITEMS



56335
Wide Steel Fish
Tape, 1/4-Inch x
25-Foot



56340
Stainless Steel Fish
Tape, 1/8-Inch x
125-Foot



56341
Stainless Steel Fish
Tape, 1/8-Inch x
240-Foot



56350
Fiberglass Fish
Tape with Spiral
Steel Leader, 50-
Foot



56382
Multi-Groove
Fiberglass Fish
Tape with Nylon
Tip, 50-Foot



[Privacy Policy](#) [Terms & Conditions](#) [Contact Us](#)

© 2020 Klein Tools, Inc. • All Rights Reserved

CUSTOMER SERVICE

1-800-553-4676

