



Proheat® Varitemp® Heat Gun & Kit



[Attachments/Accessories](#)

[Replacement Parts](#)



PH-1200 / PH-2200



Description

Videos

Downloads

Compact, lightweight, easy-to-use dial-in variable temperature heat gun

- ⌵ Models
- ⌵ Specifications

- Ergonomic design for superb balance and grip
- Variable temperature with patented electronic temperature control system
- Pre-select and maintain any temperature from 130° - 1000°F / 50° - 540°C
- Powerful airflow at 4000 FPM and 16 CFM
- Heavy-duty Lexan® plastic housing with built-in stand for hands-free use
- Protective hand/switch guard and convenient hanging loop
- Kit includes Proheat Varitemp Heat Gun, attachments 35016, 35017, 35292, 35293, 35294, and 35351 storage/carrying case
- Accessories also available separately
- Use to desolder, heat temperature sensitive materials, shrink tubing, terminate specialty connectors and more

Available Models

MODEL NO.	DESCRIPTION
PH-1200	Proheat Varitemp Heat Gun, 130°F (50°C) to 1000°F (540°C), 120V, 60 Hz, 11A, 1300W Max
PH-1200K	Proheat Varitemp Heat Gun Kit includes PH-1200 Varitemp Heat Gun, 3" spreader attachment, 1-1/3" shrink tubing attachment, 1/2" specialty connector, 9/16" reducer, and 5/16" reducer packed in a rugged storage/carrying case
PH-2200	Proheat Varitemp Heat Gun, 130°F (50°C) to 1000°F (540°C), 230V*, 50/60 Hz, 6.2A, 1426W Max CE

PH-2200K

Proheat Varitemp Heat Gun Kit includes PH-2200 Varitemp Heat Gun, 3" spreader attachment, 1-1/3" shrink tubing attachment, 1/2" specialty connector, 9/16" reducer, and 5/16" reducer packed in a rugged storage/carrying case

Specifications

Avg. Temp. 130° F to 1000° F
50°C to 540° C

Avg. Air Volume: 16 CFM/453 l/min

Avg. Air Velocity: 4000 FPM/1219m/min

Motor: Permanent Magnet

Dimensions: 8.2" L x 3.0" W x 7.3" H

Nozzle Opening: 1.3" Dia. O.D.

Nozzle Opening: 1.3" Dia. O.D.

Cordset: 6 ft., 3-wire grounded

Net Weight - Single Unit: 1.6 lbs.,

Kit: 4.5 lbs.

Shipping Weight - Single Unit: 2 lbs.,

Kit: 7 lbs.



[HEAT TOOL PRODUCTS](#)
[PARTS & SERVICE](#)
[WHERE TO BUY](#)
[DISTRIBUTORS](#)
[VIDEOS](#)

[ABOUT US](#)
[BLOG](#)
[SITEMAP](#)

©2012 Master Appliance Corp.
Master Appliance Corp.
2420 18th St.
Racine, Wisconsin 53403 USA
Phone: 262.633.7791
Toll Free: 800.558.9413
Fax: 262.633.9745

[Join Our Email List](#)

Powered by  Image Management