

RRF Rackrail



Measuring 1/8" thick, our steel RRF rack rail is threaded for 10-32 screws. With full hole spacing, they are sold in pairs and designed for use with 19 1/8" wide rough openings. Durable black powder coat finish.

A&E Spec. #96-033R [Download or view PDF file](#)

| Steel Part # | Length | Racking Height |
|--------------|---------|----------------|
| RRF2 | 3-1/2" | (2 space) |
| RRF4 | 7" | (4 space) |
| RRF6 | 10-1/2" | (6 space) |
| RRF8 | 14" | (8 space) |
| RRF10 | 17-1/2" | (10 space) |
| RRF12 | 21" | (12 space) |
| RRF14 | 24-1/2" | (14 space) |
| RRF16 | 28" | (16 space) |
| RRF18 | 31-1/2" | (18 space) |
| RRF21 | 36-3/4" | (21 space) |
| RRF27 | 47-1/4" | (27 space) |
| RRF45 | 78-3/4" | (45 space) |

NEW Aluminum rail now available, ideal for mobile, humid and marine applications. Finish in a durable black powder coat with bracketed rackspaces.



| Aluminum Part # | Length | Racking Height |
|-----------------|----------|----------------|
| RRF12AL | 21 " | (12 space) |
| RRF21AL | 36-3/4 " | (21 space) |
| RRF45AL | 78-3/4 " | (45 space) |

Cage Nut style Rackrail & Hardware

Cage Nut rackrail is available for our WMRK, WRK, MRK and DRK rack and are ideal for use with slideout servers.

| Part # | Description |
|---------------|---|
| PROWRK-RR44 | pair 44 space cage nut style rackrail for WRK Series racks |
| PROWMRK-RR42 | pair 44 space cage nut style rackrail for WMRK Series racks |
| PROWMRK-RR24 | pair 24 space cage nut style rackrail for WMRK Series racks |
| DRK19-RR44PRO | pair 44 space cage nut style rackrail for DRK Series racks |
| PROWRK-RR40 | pair 40 space cage nut style rackrail for WRK Series racks |
| PROWRK-RR37 | pair 37 space cage nut style rackrail for WRK Series racks |
| PROWRK-RR24 | pair 24 space cage nut style rackrail for WRK Series racks |
| PROMRK-RR40 | pair 40 space cage nut style rackrail for MRK Series racks |
| PROMRK-RR37 | pair 37 space cage nut style rackrail for MRK Series racks |
| PROMRK-RR24 | pair 24 space cage nut style rackrail for MRK Series racks |
| PROMRK-RR44 | pair 44 space cage nut style rackrail for MRK Series racks |
| CN6MM-100 | 100 qty 6MM cagenuts |
| CN1032-50 | 50 qty 1032 cagenuts |



Rear Hanging Brackets



These rear hanging brackets fit any amp with rear ears and attach to rear rackrail to provide additional equipment support. Sold in pairs.

| Part # | Racking Height |
|--------|------------------|
| RH-2 | 3-1/2" (2 space) |
| RH-3 | 5-1/4" (3 space) |
| RH-4 | 7" (4 space) |



RH-2