



**CABLE TIE MOUNTS (SCREW TYPE)**



**34-200-25** Disp. Pkg **34-200-100** Bulk  
**34-201-25** Disp. Pkg **34-201-100** Bulk

**ADHESIVE CABLE TIE MOUNTS**



**34-210-25** Disp. Pkg **34-210-100** Bulk  
**34-212-25** Disp. Pkg **34-212-100** Bulk

**NYLON CABLE CLAMPS**



**34-300-100** 1/8" diameter Disp. Pkg  
**34-300-1000** 1/8" diameter Bulk  
**34-302-100** 1/4" diameter Disp. Pkg  
**34-302-1000** 1/4" diameter Bulk  
**34-304-100** 3/8" diameter Disp. Pkg  
**34-304-1000** 3/8" diameter Bulk  
**34-306-100** 1/2" diameter Disp. Pkg.  
**34-306-1000** 1/2" diameter Bulk  
**34-310-100** 3/4" diameter Disp. Pkg.

**SPIRAL WRAP**

Natural color polyethylene spiral wrap. 10 Meter rolls.



**34-410-10M** 1/8" - 1/2" dia. 10 meters  
**34-420-10M** 1/4" - 2" dia. 10 meters  
**34-440-10M** 3/8" - 3" dia. 10 meters  
**34-450-10M** 1/2" - 4" dia. 10 meters

**FLEXIBLE GROMMET**

Natural color polyethylene flexible grommet. 10 M rolls.



**34-511-10M** 1/32" chassis thickness 10 meters  
**34-512-10M** 1/16" chassis thickness 10 meters  
**34-514-10M** 3/32" chassis thickness 10 meters  
**34-515-10M** 1/8" chassis thickness 10 meters

**STRAIN RELIEF BUSHINGS**

94V-2 black nylon strain relief bushings



**34-630-0** SPT-1 18/2 R/Angle .1" chassis Bulk  
**34-631-0** SPT-1 18/2 .062" chassis Bulk  
**34-632-0** SPT-1 18/2 .100" chassis Bulk  
**34-633-0** SVT 18/3 .062" chassis Bulk  
**34-634-0** SVT 18/3 .100" chassis Bulk  
**34-635-0** SJT 18/3 .062" chassis Bulk  
**34-636-0** SJT 18/3 .100" chassis Bulk  
*Available in Bulk only*

**FLEXIBLE CONDUIT**

Black polypropylene flexible conduit. Split for easy wire insertion. **Note:** Lengths vary as shown below.



Dimensions shown below are inside diameters.

**34-521-300M** 1/4" 300 meters Bulk  
**34-521-30M** 1/4" 30 meters Bulk  
**34-521-10M** 1/4" 10 meters Bulk  
**34-522-200M** 3/8" 200 meters Bulk  
**34-522-30M** 3/8" 30 meters Bulk  
**34-522-10M** 3/8" 10 meters Bulk  
**34-523-200M** 1/2" 200 meters Bulk  
**34-523-30M** 1/2" 30 meters Bulk  
**34-523-10M** 1/2" 10 meters Bulk  
**34-524-100M** 3/4" 100 meters Bulk  
**34-524-30M** 3/4" 30 meters Bulk  
**34-524-10M** 3/4" 10 meters Bulk.  
**34-525-100M** 7/8" 100 meters Bulk  
**34-525-30M** 7/8" 30 meters Bulk  
**34-525-10M** 7/8" 10 meters Bulk  
**34-526-50M** 1" 50 meters Bulk  
**34-526-10M** 1" 10 meters Bulk

**SNAP-IN BUSHINGS**

94V-2 black nylon snap-in bushings



**34-622-0** for 3/8" hole Bulk  
**34-622-50** for 3/8" hole Pkg. 50  
**34-623-0** for 1/2" hole Bulk  
**34-623-50** for 1/2" hole Pkg. 50  
**34-624-0** for 5/8" hole Bulk  
**34-624-50** for 5/8" hole Pkg. 50  
**34-625-0** for 3/4" hole Bulk  
**34-625-25** for 3/4" hole Pkg. 25  
**34-626-0** for 7/8" hole Bulk  
**34-626-25** for 7/8" hole Pkg. 25  
**34-627-0** for 1" hole Bulk  
**34-627-25** for 1" hole Pkg. 25

**HOLE PLUGS**

94V-2 black nylon hole plugs




**34-612-0** for 3/8" hole Bulk  
**34-612-50** for 3/8" hole Pkg. 50  
**34-613-0** for 1/2" hole Bulk  
**34-613-50** for 1/2" hole Pkg. 50  
**34-614-0** for 5/8" hole Bulk  
**34-614-50** for 5/8" hole Pkg. 50  
**34-615-0** for 3/4" hole Bulk  
**34-615-25** for 3/4" hole Pkg. 25  
**34-616-0** for 7/8" hole Bulk  
**34-616-25** for 7/8" hole Pkg. 25  
**34-617-0** for 1" hole Bulk  
**34-617-25** for 1" hole Pkg. 25

**STRAIN RELIEF INSTALLATION TOOL**



**34-901-1** Installation Tool Disp. Pkg.



**13-185-0**  
Universal stripping tool for round or flat Cat 5 cable.  
*Use -1 for Display Package*

**ECONOMY PUNCH-DOWN TOOL**

New Item



**13-189-0**  
Disposable punch-down tool. Suitable for 5-6mm OD UTP/STP cable.  
*Use -1 for Display Package*

**EXTRACTION TOOLS**



**37-950-1** Pkg.  
Extraction tool for .093" terminals. (37-930-0, 940)

**37-951-1** Pkg.  
Extraction tool for .062" terminals. (37-900-0, 910)


**CABLE TIE TOOL**



**34-900-0** Bulk **34-900-1** Pkg.  
Handy cable tie tensioner and cut-off tool. Made of very durable polymer material.

**MODULAR CRIMP TOOL**

Economy modular crimp tool. Cuts cable to length, strips jacket and crimps modular plug to cable. Suitable for 4P/4C and 6P/4C.



**12-294-0** Bulk  
**12-294-1** Package

**DELUXE MODULAR CRIMP TOOL**

Deluxe crimp tool cuts, strips and crimps modular plugs.



**12-306-1** 6P/4C & 6C  
**12-308-1** 8P/8C

**DESOLDERING TOOL**



**84-110-1** Desoldering tool  
**84-111-0** Replacement tip  
Suction type desoldering tool has aluminum barrel, enclosed plunger, teflon tip and is self cleaning.

**STRAIN RELIEF INSTALLATION TOOL**



**34-901-1** Installation Tool Disp. Pkg.

**SOLDERING IRON**



**84-101-1** 30 Watt soldering iron.  
**84-102-0** Replacement tips.

**SOLDERING IRON STAND**



**84-103-1**  
Sturdy soldering iron stand with tip cleaning sponge.

**'HELPING HANDS'**



**84-122-1**  
Convenient holder with heavy cast base and adjustable arms with clips.

**TWEEZERS**



**84-131-0** Stainless steel tweezers  
**84-131-1** Pkg  
125mm long, smooth inside points. High quality anti-corrosive stainless steel. Made in Japan.



**84-133-0** Bent tip tweezers  
**84-133-1** Pkg  
125mm long, serrated inside bent tips. High quality stainless steel. Made in Japan.

**STAINLESS STEEL FORCEPS**



**84-145-0** Bulk  
**84-145-1** Pkg  
125mm stainless steel curved tip clamping forceps.