


3 AMP PC RELAYS




Contact Resistance: 100mΩ max.
 Operate Time: 10ms max.
 Release Time: 5ms max.
 Insulation Resistance: 100MΩ min.
 Mechanical Life: 10M cycles
 Electrical Life: 500K cycles
 Resistive Load: 3A@28VDC or 120VAC

Part Number	Circuitry	Oper. Volt.	Coil Res.
50-330-0	SPDT	5VDC	120 Ω
50-331-0	SPDT	6VDC	180 Ω
50-333-0	SPDT	12VDC	700 Ω
50-334-0	SPDT	24VDC	2800 Ω

Use -1 for Display Package

1 AMP PC RELAYS (16-PIN DIP)





Contact Resistance: 50mΩ max.
 Operate Time: 10ms max.
 Release Time: 4ms max.
 Insulation Resistance: 100MΩ min.
 Mechanical Life: 100M cycles
 Electrical Life: 100K cycles
 Resistive Load: 1A@30VDC or .3A@125VAC

Part Number	Circuitry	Oper. Volt.	Coil Res.
50-430-0	2C	5VDC	125 Ω
50-433-0	2C	12VDC	720 Ω
50-434-0	2C	24VDC	2880 Ω
50-435-0	2C	48VDC	4600 Ω

Use -1 for Display Package

10 AMP PC RELAYS



Contact Resistance: 100mΩ max.
 Operate Time: 8ms max.
 Release Time: 5ms max.
 Insulation Resistance: 100MΩ min.
 Mechanical Life: 10M cycles
 Electrical Life: 100K cycles
 Resistive Load: 10A@28VDC or 10A@125VAC
 Inductive Load: 3A@28VDC or 3A@125VAC

Part Number	Circuitry	Oper. Volt.	Coil Res.
50-530-0	SPDT	5VDC	70 Ω
50-533-0	SPDT	12VDC	400 Ω
50-534-0	SPDT	24VDC	1600 Ω
50-535-0	SPDT	48VDC	6400 Ω

Use -1 for Display Package

PLASTIC CASES




Black plastic project boxes.

Outside dimensions shown

- 53-520-0 82L x 54W x 31H (plastic cover)
- 53-522-0 83L x 54W x 30H (alum. cover)
- 53-540-0 103L x 54W x 40H (alum. cover)

Use -1 for Display Package

Light grey ABS (UL94HB) project boxes. Self tapping screws included



New Item

- 53-530H-0 100L x 50W x 25H grey ABS plastic
- 53-535H-0 112L x 62W x 31H grey ABS plastic
- 53-551H-0 120L x 65W x 40H grey ABS plastic
- 53-571H-0 150L x 80W x 50H grey ABS plastic
- 53-581H-0 191L x 110W x 61H grey ABS plastic

Use -1 for Display Package



Inside dimensions shown

- 53-541-0 99L x 49W x 40H grey ABS plastic
- 53-551-0 125L x 60W x 40H grey ABS plastic
- 53-571-0 145L x 85W x 50H grey ABS plastic
- 53-581-0 180L x 110W x 60H grey ABS plastic

Use -1 for Display Package



- 53-918-0 275Lx182Wx40H polypropylene box with 18 compartments.