

PRODUCT CATALOG

> [Switches and Indicators](#) > [Toggle Switches](#) > [Single Pole Toggle Switches](#)

Single Pole Toggle Switches

McGill full-size, single pole toggle switches are available in several electrical ratings to meet a variety of requirements. Ruggedly constructed with metallic toggle and threaded bushing to ensure extended service life. Available with "O" ring seal in bushing for moisture resistance. All switches are UL Recognized and CSA Certified.

• 6 Amp Single Pole

6A, 125V AC;
3A, 250V AC;
1/4 HP, 125-250V AC
Suitable for 6A, 12V DC applications

• 8 Amp Single Pole

8A, 125V AC;
4A, 250V AC;
1/3 HP, 125-250V AC

• 20 Amp Single Pole

20A, 125V AC;
10A, 250V AC;
1 HP, 125-250V AC;
20A, 250V AC (non-inductive)
Suitable for 20A, 12V DC applications



3192-0003



4125-0004



90-0001

6 Amp - Available While Supplies Last

6A, 125V AC; 3A, 250V AC; 1/4HP, 125-250V AC, Suitable for 6A, 12V DC applications

6 Amp	Circuitry			Poles	Cat. No. Screw Terminal	Cat. No. Solder Terminal	Substitute for both	Note	Cat. No. 1/4" Q.C. Terminal	Substitute 1/4" Q.C.	Note
	A	B	C								
	ON	---	OFF	SPST	3190-0001	3190-0002	90-0001	Screw, 20 Amp	3190-0003	90-0001	Screw, 20 Amp
	ON	OFF	ON	SPDT	3191-0001	3191-0002	91-0001	Screw, 20 Amp	3191-0003	91-0001	Screw, 20 Amp
	ON	---	ON	SPDT	3192-0001	3192-0002	92-0001	Screw, 20 Amp	3192-0003	92-0001	Screw, 20 Amp
	(ON)	OFF	(ON)	SPDT	3193-0001	3193-0002	93-0001	Screw, 20 Amp	3193-0003	93-0001	Screw, 20 Amp
	ON	OFF	(ON)	SPDT	3193-1001	3193-1002	93-1001	Screw, 20 Amp	3193-1003	93-1001	Screw, 20 Amp

() Momentary

8 Amp

8A, 125V AC; 4A, 250V AC; 1/3HP, 125-250V AC

8 Amp	Circuitry			Poles	Cat. No. Screw Terminal	Substitute for Screw Term.	Notes	Substitute for 1/4" Q.C.	Notes	Cat. No. 6" Wire Leads
	A	B	C							
	ON	---	OFF	SPST	4125-0001	4125-0001	Screw	4125-0001	Screw	4125-0004

8 Amp - Available While Supplies Last

8A, 125V AC; 4A, 250V AC; 1/3HP, 125-250V AC

8 Amp - Available While Supplies Last	Circuitry			Poles	Cat. No. Solder Terminal	Substitute for Solder Term.	Note	Cat. No. 1/4" Q.C. Terminal	Substitute 1/4" Q.C. Terminal	Note	Catalog Number 6" Wire Leads
	A	B	C								
	ON	--	OFF	SPST	4125-0002	4125-0001	Screw	4125-0003	4125-0001	Screw	4125-0004

20 Amp

20A, 125V AC; 10A, 250V AC; 1HP, 125-250V AC; 20A, 250V AC (non-inductive)

Suitable for 20A, 12V DC applications

20 Amp	Circuitry			Poles	Cat No. Screw Terminal	Cat No. 1/4" Q.C. Terminal
	A	B	C			
	ON	---	OFF	SPST	90-0001	90-0003
	ON	OFF	ON	SPDT	91-0001	91-0003
	ON	---	ON	SPDT	92-0001	92-0003
	(ON)	OFF	(ON)	SPDT	93-0001	93-0003
	ON	OFF	(ON)	SPDT	93-1001	93-1003
	(OFF)	---	ON	SPST	93-2001	93-2003
	(ON)	---	OFF	SPST	93-3001	93-3003
	ON	---	(ON)	SPDT	93-4001	93-4003

() Momentary

20 Amp - Available While Supplies Last

20A, 125V AC; 10A, 250V AC; 1HP, 125-250V AC; 20A, 250V AC (non-inductive)

Suitable for 20A, 12V DC applications

20 Amp	Circuitry			Poles	Cat No. Solder Terminal	Substitute	Note
	A	B	C				
	ON	--	OFF	SPST	90-0002	90-0001	Screw Terminal
	ON	OFF	ON	SPDT	91-0002	91-0001	Screw Terminal
	ON	--	ON	SPDT	92-0002	92-0001	Screw Terminal
	(ON)	OFF	(ON)	SPDT	93-0002	93-0001	Screw Terminal
	ON	OFF	(ON)	SPDT	93-1002	93-1001	Screw Terminal
	(OFF)	--	ON	SPST	93-2002	93-2001	Screw Terminal
	(ON)	--	OFF	SPST	93-3002	93-3001	Screw Terminal
	ON	--	(ON)	SPDT	93-4002	93-4001	Screw Terminal

() Momentary

20 Amp with "O" ring seal - Available While Supplies Last

Single Pole Toggle Switches	Circuitry			Poles	Cat. No. Screw Terminal	Substitute
	A	B	C			
Single Pole Toggle Switches	ON	---	OFF	SPST	0090-0251	No Substitute Available

Dimensions

Switch Series	Bushings	Bats	Case
3190 & 90 Series	15/32"- 32 thread 15/32" long	9/16" long	1 11/64" x 5/8"
4125 Series	15/32"- 32 thread 9/32" long	37/64" long	1 3/64" x 39/64"

Note: Mounting hardware and terminal screws (where applicable) furnished unassembled. Mounting hardware consists of one plated hex nut and knurl nut. Indicating plate is also furnished for maintained ON-OFF circuits.