

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0444761112](#)  
**Status:** **Active**  
**Overview:** [Mini-Fit® Plus HCS](#)  
**Description:** Mini-Fit® HCS Crimp Terminal, 18-20 AWG, Bag, Copper (Cu) Alloy, Tin (Sn)

**Documents:**

[Drawing \(PDF\)](#) [Packaging Specification PK-5556-003 \(PDF\)](#)  
[Product Specification PS-44476-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family Crimp Terminals  
 Series [44476](#)  
 Application Power  
 Comments High Current  
 Crimp Quality Equipment Yes  
 Overview [Mini-Fit® Plus HCS](#)  
 Product Name Mini-Fit®  
 UPC 800754367349

**Physical**

Gender Female  
 Material - Metal High Performance Alloy (HPA)  
 Material - Plating Mating Tin  
 Material - Plating Termination Tin  
 Net Weight 0.200/g  
 Packaging Type Bag  
 Plating min - Mating 2.540µm  
 Termination Interface: Style Crimp or Compression  
 Wire Insulation Diameter 1.30-3.10mm  
 Wire Size AWG 18, 20  
 Wire Size mm² N/A


**Electrical**

Current - Maximum per Contact 11.0A

**Material Info**

**Reference - Drawing Numbers**

Packaging Specification [PK-5556-003](#)  
 Product Specification [PS-44476-001](#), [RPS-44476-001](#)



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per  
 -ED/79/2015 (17  
 December 2015)

**Halogen-Free**

**Status**

**Low-Halogen**

**Need more information on product  
 environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 Please visit the [Contact Us](#) section for any  
 non-product compliance questions.

China ROHS

ELV

Green Image

Not Relevant

**Search Parts in this Series**

[44476 Series](#)

**Application Tooling | FAQ**

*Tooling specifications and manuals are  
 found by selecting the products below.  
 Crimp Height Specifications are then  
 contained in the Application Tooling  
 Specification document.*

**Global**

Description	Product #
Hand Crimp Tool for Male and Female Crimp Terminals, 16-24 AWG Wire	<a href="#">0638190900</a>
Manual Extraction Tool	<a href="#">0638131200</a>
Extraction Tool	<a href="#">0011030044</a>

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**