

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** **1461530200**

**Status:** **Active**

**Overview:** Internet of Things (IoT) Antennas: Wi-Fi, Bluetooth, Zigbee

**Description:** 2.4GHz / 5GHz Wi-Fi Stand Alone Balance Antenna, 9.00mm Width, 200.00mm Cable Length, Compatible with U.FL / I-PEX MHF Connectors

**Documents:**

<a href="#">3D Model</a>	<a href="#">Application Specification AS-146153-100-001 (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">Packaging Specification 1461530100-000 (PDF)</a>
<a href="#">Product Specification PS-146153-100-001 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>

**General**

Product Family	Antennas
Series	146153
Component Type	Flexible Antenna with Cable
Datasheet Order No	987651-6901
Function	Signal
Mates With	Molex Receptacle <a href="#">734120110</a> and other alternatives
Overview	Internet of Things (IoT) Antennas: Wi-Fi, Bluetooth, Zigbee
Product Name	2.4/5GHz Balanced Flex Antenna
Protocol	BLE, BT, Thread, Wi-Fi, Wireless Hart, Zigbee
Type	Wi-Fi Antenna
UPC	889056310833

**Physical**

Cable Length	200.00mm
Length	34.90mm
Mounting Style	Adhesive
Net Weight	0.874/g
Packaging Type	PET Film
Polarization	Linear
Radiation Pattern	Omnidirectional
Thickness	0.10mm
Width	9.00mm


**Electrical**

Band#1 F_End (MHz)	2483.5
Band#1 F_Start (MHz)	2400
Band#2 F_End (MHz)	5930
Band#2 F_Start (MHz)	4900
Electrical Connectivity	Cable
Peak Gain (dBi)	2.6 @ 2.4 GHz, 3.5 @ 5 GHz
Return Loss - S11 (dB)	< -10
Total Efficiency	>66% @ 5 GHz, >69% @ 2.4 GHz

**Material Info**

**Reference - Drawing Numbers**

Application Specification	AS-146153-100-001
Packaging Specification	1461530100-000
Product Specification	PS-146153-100-001
Sales Drawing	SD-146153-050-001



Series image - Reference only

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per - ED/71/2019 (16 July 2019)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

146153 Series