

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0008500134](#)  
**Status:** **Active**  
**Overview:** [KK® Interconnect System - Molex](#)  
**Description:** [KK® 396 Crimp Terminal 2578, 22-26 AWG, Bag, Phosphor Bronze, Tin \(Sn\)](#)

**Documents:**

[Drawing \(PDF\)](#) [Packaging Specification PK-2759-001 \(PDF\)](#)  
[Product Specification PS-08-50-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family [Crimp Terminals](#)  
Series [2578](#)  
Application [Power](#)  
Crimp Quality Equipment [Yes](#)  
Overview [KK® Interconnect System - Molex](#)  
Packaging Alternative [08-50-0133 \(Reel\)](#)  
Product Name [KK® 396, KK® 508](#)  
UPC [800754224697](#)

**Physical**

Gender [Female](#)  
Material - Metal [Phosphor Bronze](#)  
Material - Plating Mating [Tin](#)  
Material - Plating Termination [Tin](#)  
Net Weight [0.150/g](#)  
Packaging Type [Bag](#)  
Plating min - Mating [2.540µm](#)  
Plating min - Termination [2.540µm](#)  
Termination Interface: Style [Crimp or Compression](#)  
Wire Insulation Diameter [1.65mm max.](#)  
Wire Size AWG [22, 24, 26](#)  
Wire Size mm² [N/A](#)

**Solder Process Data**

Lead-freeProcess Capability [N/A](#)

**Material Info**

Engineering Number [2578-B-\(P909\)L](#)

**Reference - Drawing Numbers**

Packaging Specification [PK-2759-001](#)  
Product Specification [PS-08-50-001](#)  
Sales Drawing [SD-2578](#)



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
ED/30/2017 (7 July  
2017)

**Halogen-Free**

**Status**

**Low-Halogen**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

**Search Parts in this Series**

[2578](#) Series

**Use With**

[2574](#) , [2139](#) , [41695](#) , [3069](#) , [6422](#) , [5265](#) ,  
[5239](#)

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**