

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0791091024**
Status: **Active**
Overview: Milli-Grid™ Connector System
Description: Milli-Grid™ Receptacle, Surface Mount, Vertical, Top/Bottom Entry, without Press-fit Plastic Pegs, without Cap, Tube, 0.38µm Gold (Au) Selective, 50 Circuits, Lead-Free

Documents:

[3D Model](#) [Product Specification TS-79109-001-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-79107-001 \(PDF\)](#)

Agency Certification

CSA LR19980
 UL E29179

General

Product Family PCB Receptacles
 Series 79109
 Application Board-to-Board, Signal
 Overview Milli-Grid™ Connector System
 Product Name Milli-Grid™
 UPC 822348490448

Physical


Circuits (Loaded) 50
 Circuits (maximum) 50
 Color - Resin Black
 Durability (mating cycles max) 50
 Flammability 94V-0
 Glow-Wire Compliant No
 Lock to Mating Part None
 Material - Metal Phosphor Bronze
 Material - Plating Mating Gold
 Material - Plating Termination Tin
 Material - Resin High Temperature Thermoplastic
 Net Weight 1.364/g
 Number of Rows 2
 Orientation Vertical
 PCB Locator No
 PCB Retention None
 Packaging Type Tube
 Pitch - Mating Interface 2.00mm
 Plating min - Mating 0.381µm
 Plating min - Termination 1.905µm
 Polarized to PCB No
 Temperature Range - Operating -55°C to +105°C
 Termination Interface: Style Surface Mount

Electrical

Current - Maximum per Contact 1.0A
 Voltage - Maximum 125V

Solder Process Data

Duration at Max. Process Temperature (seconds) 010
 Lead-free Process Capability REFLOW
 Max. Cycles at Max. Process Temperature 001
 Process Temperature max. C 260



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
 -ED/01/2017 (12
 January 2017)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

79109 Series

Mates With

Milli-Grid™ Header [87833](#) , [87832](#) , [87831](#) , [87758](#) , [87759](#) , [87760](#)
 Milli-Grid™ Low-Halogen Header [151117](#) , [151118](#) , [151119](#) , [151120](#)

Material Info

Reference - Drawing Numbers

Product Specification
Sales Drawing

PS-79107-001, TS-79109-001-001
SDA-79109-****, SDA-79109-XXXX-001

This document was generated on 07/14/2017

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION