

Honeywell Sensing and Control

Search

102TL 2-50 K
 (Home : Products : Switches » MICRO SWITCH™ Toggle Switches » TL)

narrow your search

- Products**
- Controls Monitoring and Lighting (286)
 - Machine Safety (1727)
 - Sensors (6004)
 - Switches (9781)
 - Wireless (45)

- Technology**
- Control and Instrumentation (988)
 - Electromechanical (9307)
 - Magnetic (541)
 - Platinum thin film (56)
 - Thick Film (1409)
 - More...



TL Series Toggle Switch, 2 pole, 3 position, IWTS (16-20 Gage) terminal, Locking Lever, Military Part Number MS27788-2K

Actual product appearance may vary.


[Sales & Service](#)

[Distributor Inventory](#)

[Overview](#) | [Specs](#) | [Documentation](#) | [Application Notes](#)


Product Specifications

Circuitry/Operating action



Product Type MICRO SWITCH™ Toggle Switch

Lever Lock



Ampere/Voltage Range (Resistive Load)	0.5 A at 250 Vdc, 0.5 A to 6 A at 0.5 Vac to 230 Vac, 0.5 A to 7.5 A at 0.5 Vdc to 28 Vdc, 0.75 A at 115 Vdc
Circuitry	DPDT
Action	3 position
Mounting	Bushing 15/32 in
Termination	IWTS (16-20 Gage)
MIL Spec. Number	MS27788-2K
Lever Type	Locking
UL/CSA	L192: 10 A-125, 250, 277 Vac; 1/4 Hp-125 Vac; 1/2 Hp-250, 277 Vac; 3 A-125 Vac "L"
Comment	Silver cadmium oxide contacts
Availability	Global
UNSPSC Code	30211908
UNSPSC Commodity	30211908 Toggle switches
Series Name	TL

contacts

- ▶ Customer Service
- ▶ Technical Support
- ▶ Global Sales & Service
- ▶ View Site Demo
- ▶ Site Comments?

meet dr. larry

VIDEO - Dr. Larry Goldstein explains our newest and best technologies.



▶ Meet Dr. Larry

my links

- ▶ Login to iCOM
- ▶ Login to Rep/AD Portal
- ▶ Login to Digital University

News Center

- ▶ HONEYWELL EXPANDS ITS LIMITLESS™ PLATFORM WITH THE LAUNCH OF ITS GLOBALLY AVAILABLE INDUSTRIAL WIRELESS RECEIVER
- ▶ HONEYWELL EXTENDS ITS TRUSTABILITY® PRESSURE SENSOR PRODUCT LINE WITH A SINGLE SIDE LIQUID MEDIA OPTION
- ▶ HONEYWELL ADDS NEW 100° AND 180° ARC CONFIGURATIONS TO ITS SMART POSITION SENSOR PORTFOLIO
- ▶ HONEYWELL INTRODUCES ITS HAWK™ RESOLVERS 1-INCH SERIES, FULLY HOUSED CONFIGURATION
- ▶ HONEYWELL INTRODUCES MICROPOWER OMNIPOLAR DIGITAL HALL-EFFECT SENSOR ICs WITH LOW SUPPLY VOLTAGE AND ULTRA LOW TYPICAL CURRENT



new products

New Wireless Products

Go farther. Work smarter. Explore new possibilities. Just by cutting the cord and making the switch.



[Wireless Web Site WGLA and WPMM XYR6000™](#)

[find out more](#)

white papers

- ▶ Wireless Switches Offer Unlimited Benefit
- ▶ Basic Switches Are Not Created Equal
- ▶ Applying Precision Switches
- ▶ Sensors for Medical Devices
- ▶ New Ways to Measure Torque
- ▶ Choosing Safety Switches
- ▶ Specifying Hour Meters

Need help?

[Click here to contact us](#)