

Honeywell Sensing and Control

Search

104TL 2-3F

(Home : Products : Switches » MICRO SWITCH™ Toggle Switches » TL)


narrow your search

Products

- Controls Monitoring and Lighting (286)
- Machine Safety (1727)
- Sensors (6004)
- Switches (9781)
- Wireless (45)

Technology

- Control and Instrumentation (988)
- Electromechanical (9307)
- Magnetic (541)
- Platinum thin film (56)
- Thick Film (1409)
- More...




TL Series Toggle Switch, 4 pole, 2 position, IWTS (16-20 Gage) terminal, Locking Lever, Military Part Number MS27789-23 F

Actual product appearance may vary.

[Sales & Service](#)
[Distributor Inventory](#)
[Overview](#) | [Specs](#) | [Documentation](#) | [Application Notes](#)

Product Specifications

Circuitry/Operating action



Product Type

MICRO SWITCH™ Toggle Switch

Lever Lock



Ampere/Voltage Range (Resistive Load)

0.5 A to 6 A at 0.5 Vac to 230 Vac, 0.5 A to 7.5 A at 0.5 Vdc to 28 Vdc, 0.5 A at 250 Vdc, 0.75 A at 115 Vdc

Circuitry

4PDT

Action

2 position

Mounting

Bushing 15/32 in

Termination

IWTS (16-20 Gage)

MIL Spec. Number

MS27789-23F

Lever Type

Locking

UL/CSA

L191: 15 A-125, 250, 277 Vac; 1/2 Hp-125 Vac; 1 Hp-250, 277 Vac; 5 A-120 Vac "L"

Comment

Silver cadmium oxide contacts

Availability

Global

UNSPSC Code

30211908

UNSPSC Commodity

30211908 Toggle switches

Series Name

TL

contacts

- ▶ Customer Service
- ▶ Technical Support
- ▶ Global Sales & Service
- ▶ View Site Demo
- ▶ Site Comments?

meet dr. larry

VIDEO - Dr. Larry Goldstein explains our newest and best technologies.



▶ Meet Dr. Larry

my links

- ▶ Login to iCOM
- ▶ Login to Rep/AD Portal
- ▶ Login to Digital University

News Center

- ▶ HONEYWELL EXPANDS ITS LIMITLESS™ PLATFORM WITH THE LAUNCH OF ITS GLOBALLY AVAILABLE INDUSTRIAL WIRELESS RECEIVER
- ▶ HONEYWELL ADDS NEW 100° AND 180° ARC CONFIGURATIONS TO ITS SMART POSITION SENSOR PORTFOLIO
- ▶ HONEYWELL INTRODUCES ITS HAWK™ RESOLVERS 1-INCH SERIES, FULLY HOUSED CONFIGURATION
- ▶ HONEYWELL INTRODUCES MICROPOWER OMNIPOLAR DIGITAL HALL-EFFECT SENSOR ICs WITH LOW SUPPLY VOLTAGE AND ULTRA LOW TYPICAL CURRENT
- ▶ HONEYWELL EXTENDS ITS TRUSTABILITY® PRESSURE SENSOR PRODUCT LINE WITH A SINGLE SIDE LIQUID MEDIA OPTION

