

**Honeywell Sensing and Control**

Search



**2TL28-7**  
( Home : Products : Switches » MICRO SWITCH™ Toggle Switches » TL )

**narrow your search**

- Products**
- Controls Monitoring and Lighting (352)
  - Machine Safety (1701)
  - Sensors (6224)
  - Switches (9749)
  - Wireless (39)

- Technology**
- Control and Instrumentation (1052)
  - Electromechanical (9301)
  - Magnetic (541)
  - Optical/Infrared (1042)
  - Thick Film (1764)
  - More...

**new products**

**New Wireless Products**

Go farther. Work smarter. Explore new possibilities. Just by cutting the cord and making the switch.



Wireless Web Site  
WGLA and WPMM  
XYR6000™


[find out more](#)

**white papers**

- Wireless Switches Offer Unlimited Benefit
- Basic Switches Are Not Created Equal
- Applying Precision Switches
- Sensors for Medical Devices
- New Ways to Measure Torque
- Choosing Safety Switches
- Specifying Hour Meters

**Need help?**

[Click here to contact us](#)



Actual product appearance may vary.

TL Series Toggle Switch, 2 pole, 3 position, Screw terminal, Special Design Lever


[Sales & Service](#)

[Distributor Inventory](#)

[Overview](#) [Specs](#) [Documentation](#) [Application Notes](#)

**Product Specifications**

Circuitry/Operating action



Product Type	MICRO SWITCH™ Toggle Switch
Ampere/Voltage Range (Resistive Load)	0.75 A at 115 Vdc, 0.5 A to 10 A at 0.5 Vac to 277 Vac, 0.5 A to 18 A at 0.5 Vdc to 28 Vdc, 0.5 A at 250 Vdc
Circuitry	DPDT
Action	3 position
Mounting	Bushing 15/32 in
Termination	Screw
Lever Type	Special Design
UL/CSA	L192: 10 A-125, 250, 277 Vac; 1/4 Hp-125 Vac; 1/2 Hp-250, 277 Vac; 3 A-125 Vac "L"
Comment	Delrin lever
Availability	Global
UNSPSC Code	30211908
UNSPSC Commodity	30211908 Toggle switches
Series Name	TL

**contacts**

- Customer Service
- Technical Support
- Global Sales & Service
- View Site Demo
- Site Comments?

**meet dr. larry**

**VIDEO** - Dr. Larry Goldstein explains our newest and best technologies.



Meet Dr. Larry

**my links**

- Login to iCOM
- Login to Rep/AD Portal
- Login to Digital University

**News Center**

HONEYWELL ANNOUNCES ADDITION TO RELIALIGN™ RESIDENTIAL DOOR INTERLOCK SWITCHES THAT FEATURE RUGGED, PLASTIC HOUSING

HONEYWELL RELEASES UNLIMITED POTENTIAL WITH NEW LIMITLESS™ WIRELESS SWITCHES

HONEYWELL'S XYR6000 WIRELESS POSITION SENSOR ENABLES MONITORING IN HAZARDOUS AREAS AND REMOTE LOCATIONS

**MICRO SWITCH Anniversary site**