

Datasheet for 76650-0201

General Information

Kit Part Number:	76650-0201
Connector Type:	Wire-to-Board
Solution:	Off the Board Connectors
Molex Family:	iGrid™
Certificates:	N/A
Country of Origin:	Kit assembled in U.S.A

Specifications

Circuit Size:	10, 12, 14, 16, 18
Current Rating:	1.5-2A
Mounting Style:	PCB Through Hole
Orientation:	Receptacles, Right Angle Headers
Pitch:	2.00mm (.079")
Tool Included:	No
Voltage Rating:	250V
Wire Gauge (AWG):	26-22

Product Highlights

iGrid™ wire-to-board connector system offers a compact design and anti-tangle internal lock for applications such as gaming machines, appliances, industrial and other equipment requiring good mating retention. The unique inner lock of iGrid™ prevents wire from getting tangled in the latch, compared to outer lock types where such damage may occur. The internal lock also provides space savings, an audible click and a robust design to withstand rugged handling.

Features and Benefits

- Compact design saves PCB real estate
- Fully shrouded headers withstand rugged handling and vibration
- Polarization between housing and terminal always seats properly in housing

Applications

- GPS
- Vending and Gaming machines
- HVAC
- Microwave ovens
- Medical
- Fitness equipment

Bill of Materials

Molex Part No.	Description	Quantity
501647-1100	iGrid™ Female Crimp Terminal, 26-22 AWG	200
501646-1000	2.00mm (.079") Pitch iGrid™ Receptacle, Dual Row, 10 Circuits	2
501646-1200	2.00mm (.079") Pitch iGrid™ Receptacle, Dual Row, 12 Circuits	2
501646-1400	2.00mm (.079") Pitch iGrid™ Receptacle, Dual Row, 14 Circuits	2
501646-1600	2.00mm (.079") Pitch iGrid™ Receptacle, Dual Row, 16 Circuits	2
501646-1800	2.00mm (.079") Pitch iGrid™ Receptacle, Dual Row, 18 Circuits	2
501876-1040	2.00mm (.079") Pitch iGrid™ Right Angle Header, Dual Row, 10 Circuits	2
501876-1240	2.00mm (.079") Pitch iGrid™ Right Angle Header, Dual Row, 12 Circuits	2
501876-1440	2.00mm (.079") Pitch iGrid™ Right Angle Header, Dual Row, 14 Circuits	2
501876-1640	2.00mm (.079") Pitch iGrid™ Right Angle Header, Dual Row, 16 Circuits	2
501876-1840	2.00mm (.079") Pitch iGrid™ Right Angle Header, Dual Row, 18 Circuits	2

Recommended Molex Tool

Molex Part No.	Description
63819-2300 (not included in kit)	Click for more info