

# 28061

[Products](#) > [Controls and Monitors](#) > [Operator Controls](#) > [Hour Meters](#) > [ac Hour Meters](#) > [28100 Series](#) > **28061**

## Overview

Honeywell Standard ac Hour Meter, rectangle opening, retainer mounting, 0.25 in bent blade termination, 100K hours, 22 Vac to 26 Vac operating voltage, 24 V, 60 Hz, faceplate: bla  
[View More](#)



- [view all 28061 literature](#)
- [view distributor inventory](#)
- [sample request](#)
- [email support](#)
- [get support](#)
- [email sales](#)
- [find a distributor](#)
- [email this page](#)

## Technical Specifications

|              |                  |             |            |
|--------------|------------------|-------------|------------|
| Product Type | Standard ac      | Function    | Hour Meter |
| Appearance   | Rectangle        | Mounting    | Retainer   |
| Voltage      | 22 Vac to 26 Vac | Volts ac    | 24 Vac     |
| Frequency    | 60 Hz            | Hours       | 100K       |
| Logo Top     | Hour Glass       | Logo Bottom | Hours 1/10 |

[View More](#)

View documents in:

## Documents

| TITLE   | DOCUMENT TYPE             | LANGUAGE | SIZE  |
|---|---------------------------|----------|-------|
| True Time Stamp - Hour Meters                           | Case Study                | English  | 345KB |
| Hour Meters Line Guide                                  | Product Line Guide        | English  | 571KB |
| Industrial Product Line Card                            | Line Card/Selection Chart | English  | 571KB |
| Sensors and Switches for Potential Medical Applications | Application Note          | English  | 374KB |

[View More](#)

## Applications

- Control panels
- Medical applications

### NAVIGATION LINKS

- [HOME PAGE](#)
- [PRODUCTS](#)
- [DISTRIBUTOR INVENTORY](#)
- [INDUSTRIES](#)
- [SUPPORT](#)

### DISTRIBUTOR LINKS

- [ECOM LOGIN](#)
- [LEARN CENTER](#)
- [REQUEST ACCESS TO ECOM](#)
- [SALES/AD PORTAL LOGIN](#)
- [SALES/AD PORTAL ACCESS REQUEST](#)

### LANGUAGE

### SOCIAL MEDIA



### SITE INFORMATION

[NEWS & EVENTS](#)

[ABOUT US](#)

[SAMPLE REQUEST](#)

[SUPPLIER MICROSITE](#)

[PRIVACY STATEMENT](#)

[SITEMAP](#)

[TERMS & CONDITIONS](#)

[COPYRIGHT © 2018 HONEYWELL  
INTERNATIONAL INC.](#)