

- [PRODUCTS ▾](#)
- [DISTRIBUTOR INVENTORY](#)
- [INDUSTRIES ▾](#)
- [SUPPORT ▾](#)
- [NEWS & EVENTS ▾](#)
- [ABOUT US ▾](#)

2NT1-7E

[Products](#) > [Switches](#) > [Toggle Switches](#) > [NT Series](#) > **2NT1-7E**



Overview

MICRO SWITCH NT Series Toggle Switch, 2 pole, 3 position, Screw terminal, Locking Lever.
 MICRO SWITCH NT Series toggle switches meet the ne
[View More](#)



- [view all 2NT1-7E literature](#)
- [view distributor inventory](#)
- [sample request](#)
- [email support](#)
- [get support](#)
- [email sales](#)
- [find a distributor](#)
- [email this page](#)





Technical Specifications

Series Name	NT	Product Type	MICRO SWITCH Toggle Switch
Ampere/Voltage Range (Resistive Load)	0.5 A at 250 Vdc 0.75 A at 115 Vdc 0.5 A to 18 A at 0.5 Vdc to 28 Vdc 0.5 A to 10 A at 0.5 Vac to 277 Vac	Circuitry	DPDT
Action	3 position	Circuitry/Operating action	
Mounting	Bushing 15/32 in	Termination	Screw
Lever Type	Locking	Lever Lock	 E Locked in center position

[View More](#)

View documents in:

Documents

TITLE	DOCUMENT TYPE	LANGUAGE	SIZE
 MICRO SWITCH NT Series Commercial-Grade Toggle Switches	Datasheet	English	2MB
 2NT1-7E highres photo		English	2MB
 2NT1-7E lowres photo		English	178KB
 Refrigeration Equipment – Hazardous Materials	Application Note	English	258KB

[View More](#)

Product Features

- Completely sealed switching chamber
- NEMA 3, 3R, 4, and 13
- UL recognized, File E12252, Vol. 1, Section 44
- CSA certified, File LR4442
- CE approved

Applications

- Aerial lifts, scissor lifts, truck mounted tele-handlers, and cranes
- Construction equipment
- Agriculture equipment
- Material-handling equipment
- Factory-floor control units
- Machine tool equipment manufacturers

NAVIGATION LINKS

[HOME PAGE](#)

[PRODUCTS](#)

[DISTRIBUTOR INVENTORY](#)

[INDUSTRIES](#)

[SUPPORT](#)

[NEWS & EVENTS](#)

[ABOUT US](#)

DISTRIBUTOR LINKS

[ECOM LOGIN](#)

[LEARN CENTER](#)

[REQUEST ACCESS TO ECOM](#)

[SALES/AD PORTAL LOGIN](#)

[SALES/AD PORTAL ACCESS REQUEST](#)

[SAMPLE REQUEST](#)

[SUPPLIER MICROSITE](#)

LANGUAGE

English 

SOCIAL MEDIA



SITE INFORMATION

[PRIVACY STATEMENT](#)

[SITEMAP](#)

[TERMS & CONDITIONS](#)

COPYRIGHT © 2018 HONEYWELL INTERNATIONAL INC.