



Hook-Up Wire, 300V

- [18 Gauge](#)
- [20 Gauge](#)
- [22 Gauge](#)
- [24 Gauge](#)
- [26 Gauge](#)

18 Gauge				
NTE Part No.				Color
25' Spool		100' Spool		
Solid	Stranded	Solid	Stranded	
WHS18-00-25	WH18-00-25	WHS18-00-100	WH18-00-100	Black
WHS18-01-25	WH18-01-25	WHS18-01-100	WH18-01-100	Brown
WHS18-02-25	WH18-02-25	WHS18-02-100	WH18-02-100	Red
WHS18-03-25	WH18-03-25	WHS18-03-100	WH18-03-100	Orange
WHS18-04-25	WH18-04-25	WHS18-04-100	WH18-04-100	Yellow
WHS18-05-25	WH18-05-25	WHS18-05-100	WH18-05-100	Green
WHS18-06-25	WH18-06-25	WHS18-06-100	WH18-06-100	Blue
WHS18-07-25	WH18-07-25	WHS18-07-100	WH18-07-100	Violet
WHS18-08-25	WH18-08-25	WHS18-08-100	WH18-08-100	Gray
WHS18-09-25	WH18-09-25	WHS18-09-100	WH18-09-100	White

[Back](#) | [Top](#)

20 Gauge				
NTE Part No.				Color
25' Spool		100' Spool		
Solid	Stranded	Solid	Stranded	
WHS20-00-25	WH20-00-25	WHS20-00-100	WH20-00-100	Black
WHS20-01-25	WH20-01-25	WHS20-01-100	WH20-01-100	Brown
WHS20-02-25	WH20-02-25	WHS20-02-100	WH20-02-100	Red
WHS20-03-25	WH20-03-25	WHS20-03-100	WH20-03-100	Orange
WHS20-04-25	WH20-04-25	WHS20-04-100	WH20-04-100	Yellow
WHS20-05-25	WH20-05-25	WHS20-05-100	WH20-05-100	Green
WHS20-06-25	WH20-06-25	WHS20-06-100	WH20-06-100	Blue
WHS20-07-25	WH20-07-25	WHS20-07-100	WH20-07-100	Violet
WHS20-08-25	WH20-08-25	WHS20-08-100	WH20-08-100	Gray
WHS20-09-25	WH20-09-25	WHS20-09-100	WH20-09-100	White

[Back](#) | [Top](#)

22 Gauge				
NTE Part No.				Color
25' Spool		100' Spool		
Solid	Stranded	Solid	Stranded	
WHS22-00-25	WH22-00-25	WHS22-00-100	WH22-00-100	Black
WHS22-01-25	WH22-01-25	WHS22-01-100	WH22-01-100	Brown
WHS22-02-25	WH22-02-25	WHS22-02-100	WH22-02-100	Red
WHS22-03-25	WH22-03-25	WHS22-03-100	WH22-03-100	Orange
WHS22-04-25	WH22-04-25	WHS22-04-100	WH22-04-100	Yellow
WHS22-05-25	WH22-05-25	WHS22-05-100	WH22-05-100	Green
WHS22-06-25	WH22-06-25	WHS22-06-100	WH22-06-100	Blue
WHS22-07-25	WH22-07-25	WHS22-07-100	WH22-07-100	Violet
WHS22-08-25	WH22-08-25	WHS22-08-100	WH22-08-100	Gray
WHS22-09-25	WH22-09-25	WHS22-09-100	WH22-09-100	White

[Back](#) | [Top](#)

24 Gauge				
NTE Part No.				Color
25' Spool		100' Spool		
Solid	Stranded	Solid	Stranded	
WHS24-00-25	WH24-00-25	WHS24-00-100	WH24-00-100	Black
WHS24-01-25	WH24-01-25	WHS24-01-100	WH24-01-100	Brown
WHS24-02-25	WH24-02-25	WHS24-02-100	WH24-02-100	Red
WHS24-03-25	WH24-03-25	WHS24-03-100	WH24-03-100	Orange
WHS24-04-25	WH24-04-25	WHS24-04-100	WH24-04-100	Yellow
WHS24-05-25	WH24-05-25	WHS24-05-100	WH24-05-100	Green
WHS24-06-25	WH24-06-25	WHS24-06-100	WH24-06-100	Blue
WHS24-07-25	WH24-07-25	WHS24-07-100	WH24-07-100	Violet
WHS24-08-25	WH24-08-25	WHS24-08-100	WH24-08-100	Gray
WHS24-09-25	WH24-09-25	WHS24-09-100	WH24-09-100	White

[Back](#) | [Top](#)

26 Gauge				
NTE Part No.				Color
25' Spool		100' Spool		
Solid	Stranded	Solid	Stranded	
WHS26-00-25	WH26-00-25	WHS26-00-100	WH26-00-100	Black
WHS26-01-25	WH26-01-25	WHS26-01-100	WH26-01-100	Brown
WHS26-02-25	WH26-02-25	WHS26-02-100	WH26-02-100	Red
WHS26-03-25	WH26-03-25	WHS26-03-100	WH26-03-100	Orange
WHS26-04-25	WH26-04-25	WHS26-04-100	WH26-04-100	Yellow
WHS26-05-25	WH26-05-25	WHS26-05-100	WH26-05-100	Green
WHS26-06-25	WH26-06-25	WHS26-06-100	WH26-06-100	Blue
WHS26-07-25	WH26-07-25	WHS26-07-100	WH26-07-100	Violet
WHS26-08-25	WH26-08-25	WHS26-08-100	WH26-08-100	Gray
WHS26-09-25	WH26-09-25	WHS26-09-100	WH26-09-100	White