

Soldering Irons, Butane

	Model No.	Wattage	Description	Available Tips
	J-050KT	50	50W Automatic Ignition Butane Soldering Kit. Cordless, butane powered soldering iron with an assortment of tips. Ready to use within a few seconds. Approximate temperature +400°F (+200°C) to +750°F (+400°C). Operating capacity 20 minutes at mid setting (one gas filling). Includes butane soldering iron w/ignition button, protective cap, 1.6mm conical tip, 2.4mm conical tip, chisel tip, hot knife tip, solder. Manufactured to UL standards. One year warranty.	JT-050 JT-051 JT-052
<i>New Item!</i>				
	J-080KT	80	80W Automatic Ignition Butane Soldering Kit. Cordless, butane powered soldering iron with an assortment of tips. Ready to use within a few seconds. Approximate up to +842°F (+450°C). Operating capacity 30 minutes (80% w/fuel). Includes butane soldering iron w/ignition button, protective cap, 1mm conical tip, 2.4mm conical tip, chisel tip, hot knife tip, deflector tip, solder. Manufactured to UL standards. One year warranty.	JT-080 JT-081 JT-082 JT-083
<i>New Item!</i>				
	J-220	-	Butane Stand-Up Torch. Cordless, compact torch with piezo electronic ignition. Features a 220 minute refillable butane gas tank, adjustable air flow control valve, adjustable gas flow control valve, safety KILL/OFF switch, brass body covered with protective grip and a sturdy removable base for added safety. Approximate temperature +2500°F (+1300°C). One year warranty.	-
	J-300	-	Micro-Jet. Cordless, compact torch with piezo electronic ignition, powered by a refillable butane cartridge. Approximate temperature +2500°F (+1300°C). Child resistant safety feature. Includes torch & refillable butane cartridge. One year warranty. (Butane included)	-
	J-305	-	Handy Torch. Personal compact torch with piezo electronic ignition system is ideal for camping, first aid, survival kits and everyday household repairs. Windproof and weatherproof. Adjustable flame for high or low temperatures. Approximate temperature up to +2500°F (+1300°C). Features a 20 minute gas tank.	-
<i>New Item!</i>				
	J-310L	-	Handy Torch w/LED. Personal compact torch with electronic ignition system and built-in LED is ideal for camping, first aid, survival kits and everyday household repairs. Approximate temperature +2500°F (+1300°C). Features a 30 minute gas tank.	-
	J-315BK	-	Handy Torch. Personal compact torch with piezo electronic ignition system is ideal for camping, first aid, survival kits and everyday household repairs. Windproof and weatherproof. Adjustable flame for high or low temperatures. Child resistant design. Approximate temperature up to +2500°F (+1300°C). Features a 20 minute gas tank. Available in four colors: black (BK), blue (BL), red (RD), and yellow (YL).	-
	J-315BL	-		-
	J-315RD	-		-
	J-315YL	-		-
<i>New Item!</i>				
	J-500	30-70	Butane Soldering Iron and Torch. Cordless, butane powered, pocket size soldering iron & torch ready to use within 20 seconds. Approximate temperature soldering iron +410°F (+210°C) to +750°F (+399°C) as a torch +2500°F (+1300°C). Operating capacity 30 minutes at mid setting (one gas filling). Electrical power equivalent to 30W-70W corded iron. Includes butane soldering iron, protective cap with igniter, 1mm conical tip, torch tip. Manufactured to UL standards. One year warranty.	JT-001 JT-002 JT-003 JT-012
	J-600	-	Butane Powered Glue Gun. Cordless butane powered glue gun works almost anywhere. Runs continuously for up to 100 minutes on a refillable butane energy cell. Temperature range +320°F (+160°C) to +464°F (+240°C). Uses standard 1/2" (12mm) diameter glue sticks.	-
	J-700KT	25-80	Butane Soldering Kit. Cordless, butane powered soldering iron with an assortment of tips can be used as a torch, hot blower, and hot knife. Ready to use within 20 seconds. Approximate temperature soldering iron +410°F (+210°C) to +850°F (+454°C) as a torch +2500°F (+1300°C). Operating capacity 120 minutes at mid setting (one gas filling). Electrical power equivalent to 25W-80W corded iron. Includes butane soldering iron, protective cap with igniter, 1mm conical tip, torch tip, hot blower tip, hot knife tip, solder, wiping sponge, solder stand in a convenient carrying case. Manufactured to UL standards. One year warranty.	JT-001 JT-002 JT-003 JT-012
	J-900	-	Butane Heat Gun. Cordless, flameless butane heat gun with automatic piezo electronic ignition. Approximate temperature adjusts up to +1400°F (+760°C). Operating capacity 120 minutes at mid setting (one gas filling). Includes heat gun & deflector heat shield.	-
	J-1000	-	Butane Soldering Iron. Cordless, butane powered, automatic ignition soldering iron ready to use within 20 seconds. Approximate temperature soldering iron +480°F (+249°C) to +1000°F (+538°C). Operating capacity 160 minutes of continuous use at mid-setting. Includes hot blower & deflector heat shield.	JT-005 JT-006 JT-007