

# EMF-8ES Energy Saving Power Center Surge Protector

- Automatically turns computer, TV, and other peripherals on and off
- Protects valuable equipment against surges and spikes
- Provides the highest level of equipment protection during damaging power surges
- Reduces noise interference
- Indicates if protection is still active
- Reset/off switch with built in 15 Amp circuit breaker
- Highest quality 6 foot power cord available to reduce the risk of electrical shock
- C (UL) US Listed
- Surge/Power on LED Indicator and more!

This is a must have product for those wanting to go green!

This environmentally friendly, 8 outlet Surge Protector saves up to 55% of energy used by eliminating idle current!

EMF-8ES features one master outlet that controls four connected outlets, and also has three separate transformer spaced outlets as well.

Plug your computer or television into the master outlet and plug everything else that you want to save energy into the four "connected by master" outlets. These four "connected by master" outlets turn on or off via the master outlet. This allows you to save energy and also helps to reduce greenhouse gasses!

## SPECIFICATIONS

- Electrical rating:..... 125 V, 60 Hz, 15 A, 1875 W  
Joule rating: ..... 1050 J  
Max. peak pulse current: ..... 19,500 A  
Max. surge clamping voltage: ...400 V (L - N, L - G, N - G)  
Max. surge pulse voltage: .....6000 V  
Response time: .....faster than 1 nanosecond  
EMI / RFI noise rejection: .....up to 20 dB from 150 KHz to 30 MHz  
Overload protection: ..... 125 V, 15 A circuit breaker



**NEW!**



**EMF-8ES**

# EMF-10 Digital Timer

- Turn lights on automatically at dusk and off at dawn
- Set timer for desired number of hours that your lights are on
- Automatic control of electronic equipment
- Weatherproof
- C (UL) US listed
- Auto Reset
- Overload protection
- 24 hour repetition
- Digital power indicator light and more!

This great new product allows the user to easily choose time settings ranging from one to ten hours (in one hour increments) or from dusk to dawn!

Featuring a photocell function, EMF-10 allows you to control all of your outdoor and indoor lighting and other electronic equipment as well!

Simply select your desired setting via the programmable selector button and EMF-10 will do the rest.

## SPECIFICATIONS

- Input: .....AC125V/60Hz  
Output: ..... 15 Amps Max.  
1875 Watts



**NEW!**



**EMF-10**



Distributed By:

NTE Electronics, Inc., 44 Farrand Street, Bloomfield, NJ 07003-2597  
For more information, call 973-748-5089 or visit [www.nteinc.com](http://www.nteinc.com)