

**PRODUCT FAMILIES**

- Pin Headers and Sockets
- Clips and Insulators
- Banana Plugs and Jacks
- Banana Plugs
- Banana Jacks**
- Binding Posts
- Safety Sockets
- Grabbers, Probes and Spade Terminals
- Test Leads and Patch Cords
- Coaxial Cable Assemblies
- DMM Kits

**ISO 9001:2000**

**Banana Jacks**

Mueller Electric Company is a leader in the manufacturing of Banana Jacks. View our full line below and check for available Banana Jack inventory.

**Insulated Phone Tip Banana Jack**



Model # BU-00234-\*

- Material: Banana Jack: nickel-plated brass body; Spring: nickel-plated phosphor bronze; Insulator: ABS
- Length: 1" (25mm)
- \*Std. Colors: -0 Black, -2 Red
- Rating: 15 Amps

**Insulated Banana Jack**



Model # BU-00233-\*

- Material: Banana Jack: nickel-plated brass body; Insulator: nylon
- Length: 0.66" (17mm)
- \*Std. Colors: -0 Black, -2 Red
- Rating: 15 Amps

**Pressfit Insulated Banana Jack with Solder Pin Connection**



Model # BU-31602-\*

- Material: Banana Jack: nickel-plated brass; Insulator: Dupont 101L
- Length: 1.25" (31.75mm)
- \*Std. Colors: -0 Black, -2 Red, -4 Yellow, -6 Blue
- Rating: 1000 V, 15 Amps, IEC 1010 Compliant

**Pressfit Insulated Banana Jack with Spade Connection**



Model # BU-31603-\*

- Material: Banana Jack: nickel-plated brass; Insulator: Dupont 101L
- Length: 1.37" (34.8mm)
- \*Std. Colors: -0 Black, -2 Red, -4 Yellow, -6 Blue
- Rating: 1000 V, 15 Amps, IEC 1010 Compliant

**Banana Jack**



Model # BU-32601-\*

- Material: Banana Plug: nickel-plated brass; Insulator: nylon
- Length: 2.50" (63.5mm)
- \*Std. Colors: -0 Black, -2 Red, -4 Yellow, -6 Blue
- Rating: 1000 V, 15 Amps, IEC 1010 Compliant

**SEARCH TOOLS**

**MUeller OR DISTRIBUTOR STOCK SEARCH**

PART #

**SEARCH**

---

**CROSS COMPETITOR PART #**

Choose a Brand

PART #

**SEARCH**

---

**MeterMate® DMM ACCESSORY SELECTOR**

Select Meter Make

Select a Make First

---

**BUILD A PCB HEADER OR SOCKET**

OVER 10,000 IN STOCK! **GO**