



1200 Protector

Sensitive equipment needs protection, and since 1976 the answer has been the Pelican™ Protector Case. These cases are designed rugged, and travel the harshest environments on earth. Against the extreme cold of the arctic or the heat of battle, Pelican cases have survived.

Made in the USA, these tough cases are designed with an automatic purge valve, that equalizes air pressure, a watertight silicone O-ring lid, over-molded rubber handles and stainless steel hardware.

- **Watertight, crushproof, and dustproof**
- Automatic Pressure Equalization Valve - balances interior pressure, keeps water out
- Easy open Double Throw latches
- Lifetime Guarantee of Excellence
- O-ring seal
- Open cell core with solid wall design - strong, light weight
- Pick N Pluck™ with convoluted lid foam
- Stainless steel hardware



CONFIGURATIONS



1200
Standard



1200NF
No Foam



1200WF
With Foam

DIMENSIONS

Interior (LxWxD)	9.25 x 7.12" x 4.12 (23.5 x 18.1 x 10.5 cm)
Exterior (LxWxD)	10.62 x 9.68" x 4.87 (27 x 24.6 x 12.4 cm)
Lid Depth	1.18" (3 cm)
Bottom Depth	2.93" (7.4 cm)
Total Depth	4.11" (10.4 cm)
Int Volume	0.16 ft ³ (0.005 m ³)

MATERIALS

Body	Polypropylene
Latch	ABS
O-Ring	Polymer
Pins	Stainless Steel
Foam	1.3 lb Polyurethane
Purge Body	ABS
Purge Vent	3 Micron Hydrophobic Non-Woven

COLORS



Black

Silver




Desert Tan

Yellow



Orange



OD Green

WEIGHT

Weight With Foam	2.87 lbs (1.3 kg)
Weight Empty	2.65 lbs (1.2 kg)
Buoyancy	12.02 lbs (5.5 kg)
Master Pack Weight	25.00 lbs (11.3 kg)

TEMPERATURE

Minimum Temperature	-40°F (-40 °C)
Maximum Temperature	210°F (98.9 °C)

CERTIFICATIONS

IP67
Def Stan 81-41
STANAG 4280

OTHER

Master Pack	6
Military	yes

ACCESSORIES




1201
3 pc. Replacement Foam Set



1203
Replacement O-ring



1200PF
Special Application Panel
Frame



1200TPKIT
TrekPak Case Divider Kit



1120TPDIV
Extra TrekPak Dividers



1507
Quick Mounts - set of 4



1506TSA
TSA Lock



1500D
Desiccant Silica Gel

Pelican

23215 Early Ave • Torrance, CA 90505 USA • Phone: (310) 326-4700 • (800) 473-5422 • Fax: (310) 326-3311
sales@pelican.com • www.pelican.com

