



1560 Protector

Sensitive equipment needs protection, and since 1976 the answer has been the Pelican™ Protector Case. These cases are designed rugged, and travel the harshest environments on earth. Against the extreme cold of the arctic or the heat of battle, Pelican cases have survived.

Made in the USA, these tough cases are designed with an automatic purge valve, that equalizes air pressure, a watertight silicone O-ring lid, over-molded rubber handles and stainless steel hardware.

- **Strong polyurethane wheels with stainless steel bearings**
- **Watertight, crushproof, and dustproof**
- 2 level Pick N Pluck™ with convoluted lid foam
- Automatic Pressure Equalization Valve - balances interior pressure, keeps water out
- Comfortable rubber over-molded top and side handles
- Easy open Double Throw latches
- Lifetime Guarantee of Excellence
- O-ring seal
- Open cell core with solid wall design - strong, light weight
- Retractable extension handle
- Stainless steel hardware and padlock protectors



CONFIGURATIONS



1560
Standard



1564
With Padded Dividers



1560NF
No Foam



1560TP
With TrekPak Divider System



1560WF
With Foam

DIMENSIONS

Interior (LxWxD)	19.92 x 14.98" x 9.00 (50.6 x 38 x 22.9 cm)
Exterior (LxWxD)	22.07 x 17.92" x 10.42 (56.1 x 45.5 x 26.5 cm)
Lid Depth	2.00" (5.1 cm)
Bottom Depth	7.00" (17.8 cm)
Total Depth	9" (22.9 cm)
Int Volume	1.55 ft ³ (0.044 m ³)
Padlock Hole Diameter	5/16" (8 mm)

MATERIALS

Body	Polypropylene
Latch	ABS
O-Ring	Polymer
Pins	Stainless Steel
Foam	1.3 lb Polyurethane
Purge Body	ABS
Purge Vent	3 Micron Hydrophobic Non-Woven

COLOURS

■ Black
■ Silver

■ Desert Tan
■ Yellow

■ Orange

■ OD Green

WEIGHT

Weight With Foam	20.00 lbs (9.1 kg)
Weight Empty	17.00 lbs (7.7 kg)
Buoyancy	115.00 lbs (52.2 kg)
Master Pack Weight	21.00 lbs (9.5 kg)

TEMPERATURE

Minimum Temperature	-40°F (-40 °C)
Maximum Temperature	210°F (98.9 °C)

CERTIFICATIONS

IP67
Def Stan 81-41
STANAG 4280

FOAM PROPERTIES

Layer 1 (Lid)	1.94" Convolute
Layer 2 (Base)	1.00" Pad
Layer 3 (Base)	3.00" Pick N Pluck

OTHER

Wheels	2
Extendable Handle	yes
Master Pack	1
Nameplate	yes
Military	yes

ACCESSORIES



0343
Replacement O-ring



1561
4 pc. Replacement Foam Set



1562
Pick N Pluck™ Sections Only
(set of 2)



1565
Padded Divider Set



1569
Lid Organizer



1560TPKIT
TrekPak Case Divider Kit



1560TPDIV
Extra TrekPak Dividers



1507
Quick Mounts - set of 4



1506TSA
TSA Lock



1500D
Desiccant Silica Gel



PL2
Padlock (2 pack)

Pelican

23215 Early Ave • Torrance, CA 90505 USA • Phone: (310) 326-4700 • (800) 473-5422 • Fax: (310) 326-3311
sales@pelican.com • www.pelican.com

Document created on 08-17-20