

Shrink sleeve - WMS 4,8 (EX9)R - 0800291

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Shrink sleeve, Roll, white, unlabeled, can be labeled with: THERMOMARK W, THERMOMARK ROLL, THERMOMARK X1.2, THERMOMARK ROLL X1, Unperforated, Mounting type: slide on, Cable diameter: 1.6-4.8 mm, Lettering field: 9 x 30000 mm

The figure shows the WMS 12,7 (Ex20)R version

Product Features

- Available in the form of continuous rolls and can be printed on both sides using the THERMOMARK W2 printer
- The shrink sleeves are automatically perforated or cut to the required length during the printing process
- MIL-STD-202G, SAE AMS-DTL-23053, SAE AS-81531
- CSA.C22.2 No. 198.1 (125°C, 600 V, all tubing)
- UL 224 (125°C, 600 V, all tubing)
- Individual markers can be cut to any length up to 1 m

Key Commercial Data

Packing unit	1 pc
Weight per Piece (excluding packing)	260.0 g
Custom tariff number	39173200
Country of origin	China

Technical data

Dimensions

Length (b)	30 m
Width (a)	9 mm
Cable diameter	1.6 mm ... 4.8 mm

Ambient conditions

Ambient temperature (operation)	-55 °C ... 135 °C
---------------------------------	-------------------

General

Color	white
Base element material	polyolefine
Components	Halogen-free

Shrink sleeve - WMS 4,8 (EX9)R - 0800291

Technical data

General

Material	Polyolefine
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Marking mounting type	slide on

Standards and Regulations

Connection in acc. with standard	CSA
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)

Classifications

eCl@ss

eCl@ss 4.0	24190219
eCl@ss 4.1	24190219
eCl@ss 5.0	27400401
eCl@ss 5.1	27400401
eCl@ss 6.0	27400401
eCl@ss 7.0	27400401
eCl@ss 8.0	27400401
eCl@ss 9.0	27400401

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC001530
ETIM 4.0	EC000217
ETIM 5.0	EC001530

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

Approvals

Approvals

Shrink sleeve - WMS 4,8 (EX9)R - 0800291

Approvals

Approvals

CSA / UL Recognized

Ex Approvals

Approvals submitted

Approval details

CSA 

UL Recognized 
