

## Shrink sleeve - WMS 9,5 (EX16)R - 0800293

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Shrink sleeve, Roll, white, unlabeled, can be labeled with: THERMOMARK W, THERMOMARK ROLL, THERMOMARK X1.2, THERMOMARK ROLL X1, Unperforated, Mounting type: slide on, Cable diameter: 3.2-9.5 mm, Lettering field: 16 x 20000 mm

The figure shows the WMS 12,7 (Ex20)R version

### Product Features

- Available in the form of continuous rolls and can be printed on both sides using the THERMOMARK W2 printer
- The shrink sleeves are automatically perforated or cut to the required length during the printing process
- CSA.C22.2 No. 198.1 (125°C, 600 V, all tubing)
- UL 224 (125°C, 600 V, all tubing)
- MIL-STD-202G, SAE AMS-DTL-23053, SAE AS-81531
- Individual markers can be cut to any length up to 1 m

### Key Commercial Data

Packing unit	1 pc
Weight per Piece (excluding packing)	294.2 g
Custom tariff number	39173200
Country of origin	China

### Technical data

#### Dimensions

Length (b)	20 m
Width (a)	16 mm
Cable diameter	3.2 mm ... 9.5 mm

#### Ambient conditions

Ambient temperature (operation)	-55 °C ... 135 °C
---------------------------------	-------------------

#### General

Color	white
Base element material	polyolefine
Components	Halogen-free

# Shrink sleeve - WMS 9,5 (EX16)R - 0800293

## Technical data

### General

Material	Polyolefine
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Marking mounting type	slide on

### Standards and Regulations

Connection in acc. with standard	CSA
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)

## Classifications

### eCl@ss

eCl@ss 4.0	24190219
eCl@ss 4.1	24190219
eCl@ss 5.0	27400401
eCl@ss 5.1	27400401
eCl@ss 6.0	27400401
eCl@ss 7.0	27400401
eCl@ss 8.0	27400401

### ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC001530
ETIM 4.0	EC000217
ETIM 5.0	EC001530

### UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

## Approvals

### Approvals

---

### Approvals

CSA / UL Recognized

## Shrink sleeve - WMS 9,5 (EX16)R - 0800293

### Approvals

---

Ex Approvals

---

Approvals submitted

---

### Approval details

