

## Sealing frame - CES-B16-HFFS-PLBK - 0801662

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Sealing frame with locking latch, size B16, with flat gasket, for 8 small sleeves

### Product Description

Including flat gasket; mounting screws not supplied as standard



### Key Commercial Data

Packing unit	1 pc
Weight per Piece (excluding packing)	140.0 g
Custom tariff number	85472000
Country of origin	Poland

### Technical data

#### Dimensions

Length	120 mm
Width	58.5 mm
Height	20 mm

#### Ambient conditions

Degree of protection	IP44
Ambient temperature (operation)	-40 °C ... 120 °C

#### General

Product description	Including flat gasket; mounting screws not supplied as standard
Frame type	Sealing frame
Material	PA
Flammability rating according to UL 94	V0
Color	black
Torque	1.8 Nm (Mounting screw, M4 (ISO 4762/DIN 912))

# Sealing frame - CES-B16-HFFS-PLBK - 0801662

## Technical data

### General

Installation instructions	One large sleeve requires the space of 4 small sleeves, M4 mounting screws (ISO 4762/DIN 912), torque for mounting screw: 1.8 Nm
	A video tutorial on how to assemble the product can be found in the Downloads area, in the Video category.
	Leak-tightness is guaranteed with underwall and perpendicular mounting; the flat gasket should be inserted between the wall and the sealing frame in the case of wall mounting.

### Standards and Regulations

Connection in acc. with standard	CUL
Flammability rating according to UL 94	V0

### Classifications

#### eCl@ss

eCl@ss 4.0	23110102
eCl@ss 4.1	23110102
eCl@ss 5.0	23110102
eCl@ss 5.1	23110102
eCl@ss 6.0	23110102
eCl@ss 7.0	23110102
eCl@ss 8.0	27142421

#### ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC002498
ETIM 5.0	EC000211

#### UNSPSC

UNSPSC 6.01	27113201
UNSPSC 7.0901	27113201
UNSPSC 11	27113201
UNSPSC 12.01	27113201
UNSPSC 13.2	27113201

### Approvals

#### Approvals

# Sealing frame - CES-B16-HFFS-PLBK - 0801662

## Approvals

Approvals

UL Recognized / cUL Recognized / GL / cULus Recognized

---

Ex Approvals

---

Approvals submitted

---

## Approval details

UL Recognized


cUL Recognized

GL

cULus Recognized


## Drawings

Dimensional drawing



Dimensional drawing

Dimensional drawing



Panel cutout

