

## Fuse plug - ST-SILED 24-UK 4 - 0921037

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Fuse plug, Nominal current: 6.3 A, Length: 33.1 mm, Width: 6.1 mm, Height: 45.7 mm, Color: black

The illustration shows the version without LED/light indicator

### Key Commercial Data

|                                      |  |
|--------------------------------------|--|
| Packing unit                         | 1 pc   |
| GTIN                                 | <br>4 017918 010294 |
| Weight per Piece (excluding packing) | 5.88 g   |
| Custom tariff number                 | 85363010   |
| Country of origin                    | Poland   |

### Technical data

#### General

|  |  |
|--|--|
| Note                                   | If the fuse is defective, the downstream circuit is not off load |
| Color                                  | black  |
| Insulating material                    | PA   |
| Flammability rating according to UL 94 | V2   |

#### Dimensions

|        |         |
|--------|---------|
| Width  | 6.1 mm  |
| Length | 33.1 mm |

#### General

|  |            |
|--|------------|
| Fuse   | G / 5 x 20 |
| Insulating material group  | CTI 600    |
| Nominal current $I_N$  | 6.3 A      |
| Nominal voltage $U_N$  | 24 V       |
| Relative insulation material temperature index (Elec., UL 746 B) | 130 °C     |

# Fuse plug - ST-SILED 24-UK 4 - 0921037

## Technical data

### Connection data

|                   |                 |
|-------------------|-----------------|
| Connection method | Plug connection |
|-------------------|-----------------|

### Standards and Regulations

|  |     |
|--|-----|
| Connection in acc. with standard       | CSA |
| Flammability rating according to UL 94 | V2  |

## Classifications

### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 4.0 | 27141199 |
| eCl@ss 4.1 | 27141199 |
| eCl@ss 5.0 | 27141145 |
| eCl@ss 5.1 | 27141145 |
| eCl@ss 6.0 | 27141149 |
| eCl@ss 7.0 | 27141149 |
| eCl@ss 8.0 | 27142001 |

### ETIM

|          |          |
|----------|----------|
| ETIM 2.0 | EC000897 |
| ETIM 3.0 | EC000897 |
| ETIM 4.0 | EC002018 |
| ETIM 5.0 | EC000036 |

### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 30211811 |
| UNSPSC 7.0901 | 39121409 |
| UNSPSC 11     | 39121409 |
| UNSPSC 12.01  | 39121409 |
| UNSPSC 13.2   | 39121409 |

## Approvals

### Approvals

---

#### Approvals

CSA / UL Recognized / cUL Recognized / EAC / cULus Recognized

---

# Fuse plug - ST-SILED 24-UK 4 - 0921037

## Approvals


Ex Approvals


---


Approvals submitted

---


### Approval details

|   |       |
|---|-------|
| CSA  |       |
| Nominal current IN  | 10 A  |
| Nominal voltage UN  | 300 V |

|   |       |
|---|-------|
| UL Recognized  |       |
| Nominal current IN  | 6.3 A |
| Nominal voltage UN  | 300 V |

|  |       |
|--|-------|
| cUL Recognized  |       |
| Nominal current IN   | 6.3 A |
| Nominal voltage UN   | 300 V |

|     |
|-----|
| EAC |
|-----|

|  |
|--|
| cULus Recognized  |
|--|