

Crimping pliers - CRIMPFOX 50R - 1212041

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Crimping pliers, for ferrules without insulating collar according to DIN 46228 Part 1 and ferrules with insulating collar according to DIN 46228 Part 4, 35 mm² ... 50 mm², lateral entry, WM crimp

Your advantages

- Ergonomically designed handles ensure an optimum grip and reduce the amount of force required by 25%



Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 453912
GTIN	4046356453912
Weight per Piece (excluding packing)	680.000 g
Custom tariff number	82032000
Country of origin	Sweden

Technical data

Dimensions

Length (b)	256 mm
Width (a)	25 mm
Height (c)	68 mm

General

Color	black
Compression	WM crimp
Type of contact	Insulated and uninsulated ferrules
Designation	Crimping position 1
Max. cross section	35 mm ²
AWG min	2

Crimping pliers - CRIMPFOX 50R - 1212041

Technical data

General

AWG max	1
Designation	Crimping position 2
Max. cross section	50 mm ²
AWG max	1
Designation	Crimping position 3
Die station	Crimping position 4
	Crimping position 5
Weight	578 g
Min. cross section	35 mm ²
Max. cross section	50 mm ²
AWG min	2
AWG max	1

Environmental Product Compliance

California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration
---------------------------	---

Classifications

eCl@ss

eCl@ss 10.0.1	21043811
eCl@ss 4.0	21040300
eCl@ss 4.1	21040300
eCl@ss 5.0	21040300
eCl@ss 5.1	21040300
eCl@ss 6.0	21043800
eCl@ss 7.0	21043811
eCl@ss 8.0	21043811
eCl@ss 9.0	21043811

ETIM

ETIM 2.0	EC001186
ETIM 3.0	EC001186
ETIM 4.0	EC001186
ETIM 5.0	EC000168
ETIM 6.0	EC000168
ETIM 7.0	EC000168

Crimping pliers - CRIMPFOX 50R - 1212041

Classifications

UNSPSC

UNSPSC 6.01	27112118
UNSPSC 7.0901	27111518
UNSPSC 11	23171604
UNSPSC 12.01	27111518
UNSPSC 13.2	27111518
UNSPSC 18.0	27111518
UNSPSC 19.0	27111518
UNSPSC 20.0	27111518
UNSPSC 21.0	27111518

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approval details

EAC		RU x- DE.xx08.B.02974
-----	--	--------------------------

Accessories

Accessories

Die

Replacement die - CRIMPFOX 50R/DIE - 1212042



Spare die, for CRIMPFOX 50R

Crimping pliers - CRIMPFOX 50R - 1212041

Accessories

Mounting material

Replacement spring - CRIMPFOX/ SPR-1 - 1212069



Spare recuperating spring