

Crimping pliers - CRIMPFOX-TC MP - 1212510

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Crimping pliers, for turned contacts, universal cross section setting, up to a maximum of 2.5 mm², digital display with 0.01 mm increments, pressure lock can be unlocked, including positioning tool

Your advantages

- ✓ Universal adjustment for precise processing of corresponding cross sections
- ✓ Crimping pliers for processing turned contacts of up to 2.5 mm²
- ✓ The integrated positioning tool ensures that the contacts are perfectly aligned



Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 555500
GTIN	4046356555500
Weight per Piece (excluding packing)	820.000 g
Custom tariff number	82032000
Country of origin	Germany

Technical data

Dimensions

Length (b)	175 mm
------------	--------

General

Color	black
Compression	Four-mandrel crimping
Type of contact	Turned contacts

Crimping pliers - CRIMPFOX-TC MP - 1212510

Technical data

General

Weight	850 g
Min. cross section	0.08 mm ²
Max. cross section	2.5 mm ²
AWG min	28
AWG max	14


Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50 years
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"
California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration

Drawings

Crimping pliers - CRIMPFOX-TC MP - 1212510

Pictogram



Classifications

eCl@ss

eCl@ss 10.0.1	21043811
eCl@ss 4.0	21040300
eCl@ss 4.1	21040300
eCl@ss 5.0	21040300
eCl@ss 5.1	21040300
eCl@ss 6.0	21043800
eCl@ss 7.0	21043811

Crimping pliers - CRIMPFOX-TC MP - 1212510

Classifications

eCl@ss

eCl@ss 8.0	21043811
eCl@ss 9.0	21043811

ETIM

ETIM 2.0	EC001186
ETIM 3.0	EC001186
ETIM 4.0	EC001186
ETIM 5.0	EC000168
ETIM 6.0	EC000168
ETIM 7.0	EC000168

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	27111518
UNSPSC 18.0	27111518
UNSPSC 19.0	27111518
UNSPSC 20.0	27111518
UNSPSC 21.0	27111518

Approvals


Approvals

Approvals

EAC

Ex Approvals

Approval details

EAC		RU x- DE.xx08.B.02974
-----	---	--------------------------

Crimping pliers - CRIMPFOX-TC MP - 1212510

Accessories

Accessories

Crimping tool

Spare locator - CRIMPFOX-TC MP LOC - 1045123



Locator for CRIMPFOX-TC MP6