

## Crimping pliers - CRIMPFOX-RCI 6-M - 1212730

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Crimping pliers, compact pliers, for symmetrical insulated cable lugs, 0.5 mm<sup>2</sup> ... 6.0 mm<sup>2</sup> (red, blue, yellow), three marked die stations, unlockable pressure lock, lateral entry

### Your advantages

- Crimping pliers for cable lugs and connectors
- They unlock as soon as the required crimping pressure is reached, therefore ensuring sufficient pressure is applied.
- The color-coded dies clearly indicate the cross section.
- Unlockable pressure lock

### Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 857895
GTIN	4046356857895
Weight per Piece (excluding packing)	620.000 g
Custom tariff number	82032000
Country of origin	Sweden

### Technical data

#### Dimensions

Length (b)	204 mm
Width (a)	22 mm
Height (c)	76 mm

#### General

Color	black
Compression	Oval crimp
Type of contact	Insulated cable lugs
Min. cross section	0.5 mm <sup>2</sup>
Max. cross section	1.5 mm <sup>2</sup>

# Crimping pliers - CRIMPFOX-RCI 6-M - 1212730

## Technical data

### General

AWG min	20
AWG max	16
Weight	500 g
Min. cross section	0.5 mm <sup>2</sup>
Max. cross section	6 mm <sup>2</sup>
AWG min	20
AWG max	10

### Environmental Product Compliance

California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration
---------------------------	---

## Classifications

### eCl@ss

eCl@ss 10.0.1	21043811
eCl@ss 4.0	21040300
eCl@ss 4.1	21040300
eCl@ss 5.0	21040300
eCl@ss 5.1	21040300
eCl@ss 6.0	21043800
eCl@ss 7.0	21043811
eCl@ss 8.0	21043811
eCl@ss 9.0	21043811

### ETIM

ETIM 3.0	EC001186
ETIM 4.0	EC000168
ETIM 5.0	EC000168
ETIM 6.0	EC000168
ETIM 7.0	EC000168

### UNSPSC

UNSPSC 6.01	27112118
UNSPSC 7.0901	27111518
UNSPSC 11	23171604
UNSPSC 12.01	27111518
UNSPSC 13.2	27111518
UNSPSC 18.0	27111518

# Crimping pliers - CRIMPFOX-RCI 6-M - 1212730

## Classifications

### UNSPSC

UNSPSC 19.0	27111518
UNSPSC 20.0	27111518
UNSPSC 21.0	27111518

## Approvals

### Approvals

---

### Approvals


### EAC

---

### Ex Approvals

---

## Approval details

EAC		RU x- DE.xx08.B.02974
-----	---	--------------------------