

## Membrane keypad - KP HCS T-MIC K12 C3 P9 - 2203567

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Membrane keypad, self-adhesive, silver conduction technology, 12 keys, embossed, 3 colors, connection cable: 88.5 mm, with crimp female connector RM 2.54 mm, operating temperature -20 °C ... 70 °C

### Your advantages

- ✓ Easy integration into electronics housings of the HCS and DCS series
- ✓ Membrane keypads in various sizes and colors for customized device designs
- ✓ Customer-specific key layouts on request

### Key Commercial Data

Packing unit	1 pc
GTIN	 4 055626 474007
GTIN	4055626474007
Weight per Piece (excluding packing)	20.000 g
Custom tariff number	85371098
Country of origin	Germany

### Technical data

#### Product properties

Type	KP HCS T-MIC K12 C3 P9
Order No.	2203567
Mounting type	adhesive
Number of positions	9
Number of keys	12 (2 x 6)
Number of socket pins	9
Technology	Conductive silver technology

# Membrane keypad - KP HCS T-MIC K12 C3 P9 - 2203567

## Technical data

### Product properties

Embossing	Dome embossing 10 x 10 mm
-----------	---------------------------

### Dimensions

Dimensions	38 mm x 140 mm
Pitch	2.54 mm
Length	88.5 mm (Membrane cable)

### Ambient conditions

Ambient temperature (storage/transport)	-20 °C ... 70 °C
Ambient temperature (operation)	-40 °C ... 80 °C

### Packaging details

Pieces per package	1
Denomination packing units	Pcs.

## Classifications

### eCl@ss

eCl@ss 10.0.1	27182702
eCl@ss 5.1	27180506
eCl@ss 6.0	27180800
eCl@ss 7.0	27182702
eCl@ss 8.0	27182702
eCl@ss 9.0	27182702

### ETIM

ETIM 5.0	EC001031
ETIM 6.0	EC001031
ETIM 7.0	EC001031

## Accessories

### Additional products

Electronic housing - HCS-T MICRO X C 1 1 7035 - 2203126



Handheld housing, T-Micro, light gray, consisting of two half shells, two front plates with screws, front 1.1 mm recessed, closed with keypad slot

## Membrane keypad - KP HCS T-MIC K12 C3 P9 - 2203567

### Accessories

Electronic housing - HCS-T MICRO X 2AA C C 7035 - 2203127



Handheld housing, T-Micro, light gray, consisting of two half shells, screws, front 1.1 mm recessed, closed with keypad slot, battery compartment cover and battery contacts, for 2 AA batteries

---

Electronic housing - HCS-T MICRO X 2AA 1 1 7035 - 2203128



Handheld housing, T-Micro, light gray, consisting of two half shells, two front plates, screws. Front 1.1 mm recessed, closed with keypad slot, battery compartment cover and battery contacts for 2 AA batteries