

Profile - UM-ALU 4-100,5 PROFILE 235 - 2200941

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Press-drawn section housings, Basic profile, height: 105 mm

Your advantages

- ✔ Item is from the UM-ALU product range
- ✔ Aluminum press-drawn section
- ✔ Available in lengths from 42.5 mm ... 990 mm, can be cut to any length
- ✔ Available in overall widths of 75 mm and 105 mm
- ✔ Variety of connection technologies
- ✔ Can be mounted on the DIN rail
- ✔ EMC protection

Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 716406
GTIN	4046356716406
Weight per Piece (excluding packing)	280.000 g
Custom tariff number	76042990
Country of origin	Germany

Technical data

Product properties

Brief article description	Profile
Type	UM-ALU 4-100,5 PROFILE 235
Order No.	2200941

Profile - UM-ALU 4-100,5 PROFILE 235 - 2200941

Technical data

Product properties

Housing type	Press-drawn section housings
Type	Basic profile

Dimensions

Length	235 mm
Height	105 mm
Depth	29.4 mm
Depth from top edge of DIN rail	25.5 mm

Material specifications

Housing material	Aluminum
Color (RAL)	aluminum color
Surface characteristics	anodized

Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
---------------------------------	-------------------

Packaging specifications


Pieces per package	1
Denomination packing units	Pcs.

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Drawings

Dimensional drawing



Profile - UM-ALU 4-100,5 PROFILE 235 - 2200941

Classifications

eCl@ss

eCl@ss 10.0.1	27182701
eCl@ss 4.0	27180400
eCl@ss 4.1	27180400
eCl@ss 5.0	27180500
eCl@ss 5.1	27180500
eCl@ss 6.0	27182000
eCl@ss 7.0	27182701
eCl@ss 8.0	27182701
eCl@ss 9.0	27182701

ETIM

ETIM 3.0	EC001031
ETIM 4.0	EC000721
ETIM 5.0	EC002779
ETIM 6.0	EC002779
ETIM 7.0	EC002779

UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501

Accessories

Necessary add-on products

Side element - UM-ALU 4-100,5 COVER AL - 2200951

Press-drawn section housings, Side elements (left and right), incl. snap-on foot, width: 105 mm



Profile - UM-ALU 4-100,5 PROFILE 235 - 2200941

Accessories

Side element - UM-ALU 4-100,5 COVERLID 45 AL - 2201759

Press-drawn section housings, Side elements (left and right), incl. snap-on foot, width: 105 mm



Side element - UM-ALU 4-100,5 COVERLID 75 AL - 2201760

Press-drawn section housings, Side elements (left and right), incl. snap-on foot, width: 105 mm



Base latch - UM-ALU 4 FOOT - 2200974



Press-drawn section housings, Snap-on foot for DIN rail, incl. screw

Additional products

Profile cover - UM-ALU 4 AU45 L235 - 2200960



Press-drawn section housings, Profile cover, width: 45 mm

Profile cover - UM-ALU 4 AU75 L235 - 2200969



Press-drawn section housings, Profile cover, width: 75 mm

Profile - UM-ALU 4-100,5 PROFILE 235 - 2200941

Accessories

Front plate - UM-ALU 4-100,5 FRONT 235 AP - 2202101



Press-drawn section housings, Basic profile front plate, width: 101.8 mm

Phoenix Contact 2019 © - all rights reserved
<http://www.phoenixcontact.com>