

Plug-in bridge - FBS 3-6 BU - 3036945

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (http://phoenixcontact.com/download)



Plug-in bridge, pitch: 6.2 mm, width: 16.9 mm, number of positions: 3, color: blue

Your advantages

The 2- to 50-pos. jumpers can bridge up to 50 terminal blocks in the two bridge shafts of the CLIPLINE complete system in one step



Key Commercial Data

Packing unit	1 pc
Minimum order quantity	50 pc
GTIN	4 017918 930288
GTIN	4017918930288
Weight per Piece (excluding packing)	2.950 g
Custom tariff number	85366990
Country of origin	Germany

Technical data

Technical data

Color	blue
Color	blue
Material	Copper
Number of positions	3
Pitch	6.2 mm
Height	23 mm
Width	16.9 mm
Flammability rating according to UL 94	V0



Plug-in bridge - FBS 3-6 BU - 3036945

Technical data

Technical data

Maximum load current	32 A (The current values for the jumpers can deviate when used in different modular terminal blocks. The precise values can be found in the accessories data for the respective modular terminal blocks.)	
Standards and Regulations		
Flammability rating according to UL 94	V0	
Environmental Product Compliance		
China RoHS	Environmentally friendly use period: unlimited = EFUP-e	
	No hazardous substances above threshold values	

Classifications

eCl@ss

eCl@ss 4.1	27141100
eCl@ss 5.1	27141100
eCl@ss 6.0	27141100
eCl@ss 7.0	27141140
eCl@ss 8.0	27141140
eCl@ss 9.0	27141140

ETIM

ETIM 2.0	EC000489
ETIM 3.0	EC000489
ETIM 4.0	EC000489
ETIM 5.0	EC000489
ETIM 6.0	EC000489
ETIM 7.0	EC000489

UNSPSC

UNSPSC 6.01	30211829
UNSPSC 7.0901	39121426
UNSPSC 11	39121426
UNSPSC 12.01	39121426
UNSPSC 13.2	39121426

Approvals

Approvals



Plug-in bridge - FBS 3-6 BU - 3036945

Approvals		
Approvals		
EAC / EAC		
Ex Approvals		
Approval details		
EAC	EAC	EAC-Zulassung
EAC	EAC	RU C- DE.A*30.B.01742

Accessories

Accessories

Cutting tools

Front cutter - CUTFOX-FBS - 1212124



 $Cutting \ tool, for \ separating \ individual \ jumper \ bars \ from \ FBS \ ... \ plug-in \ bridges \ and \ EB \ ... \ insertion \ bridges$

Protective cap

Protective cap - FBSC - 3012325



Covering hood, provides reliable shock protection when using cut-to-length FBS ...-5 and FBS ...-6 bridges, color: red