

## Thermal transfer printer set - THERMOFOX SET - 0803986

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Portable thermal transfer printer for materials off the roll, with accessories (adapter, battery, USB cable, MM-EMLF (18XE) WH/BK and EMLC (18xE) WH/BK materials) in hard-shell case

### Your advantages

- ✓ Maintenance-free operation with proven thermal transfer printing technology
- ✓ Easy to control with the PROJECT COMPLETE software
- ✓ Printing of self-adhesive, non-sticky labels and shrink sleeves
- ✓ The THERMOFOX prints materials in cassette format, which contain the material to be marked and the appropriate ink ribbon.
- ✓ Intuitive user guidance thanks to a well-structured menu and direct input keys
- ✓ 8 different barcodes and over 300 symbols can be integrated.
- ✓ Alternative control via the CLIP PROJECT software

### Key Commercial Data

|                                      |   |
|--------------------------------------|---|
| Packing unit                         | 1 pc  |
| GTIN                                 | <br>4 055626 212609 |
| GTIN                                 | 4055626212609   |
| Weight per Piece (excluding packing) | 2,420.000 g   |
| Custom tariff number                 | 84433210  |
| Country of origin                    | China   |

### Technical data

#### General

|           |       |
|-----------|-------|
| Interface | USB   |
| Weight    | 656 g |

#### Dimensions

# Thermal transfer printer set - THERMOFOX SET - 0803986

## Technical data

### Dimensions

|        |        |
|--------|--------|
| Length | 230 mm |
| Height | 69 mm  |
| Width  | 98 mm  |

### Connection data

|                 |          |
|-----------------|----------|
| Minimum voltage | 100 V AC |
| Max. voltage    | 240 V AC |
| Additional text | 50/60 Hz |

### Environmental Product Compliance

|                           |   |
|---------------------------|---|
| REACH SVHC                | Lead 7439-92-1  |
| China RoHS                | For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"           |
| California Proposition 65 | Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration |

## Classifications

### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 4.0 | 27060700 |
| eCl@ss 4.1 | 27060700 |
| eCl@ss 5.0 | 27400200 |
| eCl@ss 5.1 | 27400200 |
| eCl@ss 6.0 | 19140100 |
| eCl@ss 7.0 | 19140104 |
| eCl@ss 8.0 | 19140104 |
| eCl@ss 9.0 | 19140104 |

### ETIM

|          |          |
|----------|----------|
| ETIM 2.0 | EC000761 |
| ETIM 3.0 | EC000761 |
| ETIM 4.0 | EC000005 |
| ETIM 5.0 | EC001672 |
| ETIM 6.0 | EC001672 |
| ETIM 7.0 | EC001672 |

### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 27121706 |
| UNSPSC 7.0901 | 27121706 |

# Thermal transfer printer set - THERMOFOX SET - 0803986

## Classifications

### UNSPSC

|              |          |
|--------------|----------|
| UNSPSC 11    | 27121706 |
| UNSPSC 12.01 | 27121706 |
| UNSPSC 13.2  | 43212108 |
| UNSPSC 18.0  | 43212108 |
| UNSPSC 19.0  | 43212108 |
| UNSPSC 20.0  | 43212108 |
| UNSPSC 21.0  | 43212108 |

## Approvals

### Approvals

---

### Approvals

EAC

---

### Ex Approvals

---

### Approval details

|     |  |                          |
|-----|--|--------------------------|
| EAC |  | RU D-<br>DE.ME06.B.02060 |
|-----|--|--------------------------|

## Accessories

### Accessories

#### Conductor marking

Cable marker label - MM-WML 3 (EX10)R C1 WH/BK - 0803931



Cable marker label, Roll, white, can be labeled with: THERMOFOX: without print, mounting type: adhesive, lettering field size: continuous x 10 mm

## Thermal transfer printer set - THERMOFOX SET - 0803986

### Accessories

Cable marker label - MM-WML 5 (EX10)R C1 WH/BK - 0803932



Cable marker label, Roll, white, can be labeled with: THERMOFOX: without print, mounting type: adhesive, lettering field size: continuous x 10 mm

---

### Device marking

Label, highly flexible - MM-EMLF (EX18)R C1 GN/WH - 0803953



Highly flexible label, continuous, cassette, green with white imprint, mounting type: adhesive, can be marked with THERMOFOX

---

Label, highly flexible - MM-EMLF (EX24)R C1 GN/WH - 0803954



Highly flexible label, continuous, cassette, green with white imprint, mounting type: adhesive, can be marked with THERMOFOX

---

Label, highly flexible - MM-EMLF (EX10)R C1 OG/BK - 0803955



Highly flexible label, continuous, cassette, orange with black imprint, mounting type: adhesive, can be marked with THERMOFOX

---

Label, highly flexible - MM-EMLF (EX12)R C1 OG/BK - 0803956



Highly flexible label, continuous, cassette, orange with black imprint, mounting type: adhesive, can be marked with THERMOFOX

---

## Thermal transfer printer set - THERMOFOX SET - 0803986

### Accessories

Label, highly flexible - MM-EMLF (EX18)R C1 OG/BK - 0803957



Highly flexible label, continuous, cassette, orange with black imprint, mounting type: adhesive, can be marked with THERMOFOX

---

Label, highly flexible - MM-EMLF (EX24)R C1 OG/BK - 0803958



Highly flexible label, continuous, cassette, orange with black imprint, mounting type: adhesive, can be marked with THERMOFOX

---

Label, highly flexible - MM-EMLF (EX10)R C1 RD/WH - 0803959



Highly flexible label, continuous, cassette, red with white imprint, mounting type: adhesive, can be marked with THERMOFOX

---

Fabric label - MM-EMLC (EX10)R C1 WH/BK - 0803933



Highly flexible textile label, continuous, cassette, white with black imprint, mounting type: adhesive, can be marked with THERMOFOX

---

Fabric label - MM-EMLC (EX12)R C1 WH/BK - 0803934



Highly flexible textile label, continuous, cassette, white with black imprint, mounting type: adhesive, can be marked with THERMOFOX

---

## Thermal transfer printer set - THERMOFOX SET - 0803986

### Accessories

Fabric label - MM-EMLC (EX18)R C1 WH/BK - 0803936



Highly flexible textile label, continuous, cassette, white with black imprint, mounting type: adhesive, can be marked with THERMOFOX

---

Label, highly flexible - MM-EMLF (EX10)R C1 WH/BK - 0803937



Highly flexible label, continuous, cassette, white with black imprint, mounting type: adhesive, can be marked with THERMOFOX

---

Label, highly flexible - MM-EMLF (EX12)R C1 WH/BK - 0803938



Highly flexible label, continuous, cassette, white with black imprint, mounting type: adhesive, can be marked with THERMOFOX

---

Label, highly flexible - MM-EMLF (EX18)R C1 WH/BK - 0803939



Highly flexible label, continuous, cassette, white with black imprint, mounting type: adhesive, can be marked with THERMOFOX

---

Label, highly flexible - MM-EMLF (EX24)R C1 WH/BK - 0803940



Highly flexible label, continuous, cassette, white with black imprint, mounting type: adhesive, can be marked with THERMOFOX

---

## Thermal transfer printer set - THERMOFOX SET - 0803986

### Accessories

Label, highly flexible - MM-EMLF (EX10)R C1 YE/BK - 0803941



Highly flexible label, continuous, cassette, yellow with black imprint, mounting type: adhesive, can be marked with THERMOFOX

---

Label, highly flexible - MM-EMLF (EX12)R C1 YE/BK - 0803942



Highly flexible label, continuous, cassette, yellow with black imprint, mounting type: adhesive, can be marked with THERMOFOX

---

Label, highly flexible - MM-EMLF (EX18)R C1 YE/BK - 0803943



Highly flexible label, continuous, cassette, yellow with black imprint, mounting type: adhesive, can be marked with THERMOFOX

---

Label, highly flexible - MM-EMLF (EX24)R C1 YE/BK - 0803944



Highly flexible label, continuous, cassette, yellow with black imprint, mounting type: adhesive, can be marked with THERMOFOX

---

Label, highly flexible - MM-EMLF (EX10)R C1 BU/WH - 0803945



Highly flexible label, continuous, cassette, blue with white imprint, mounting type: adhesive, can be marked with THERMOFOX

---

## Thermal transfer printer set - THERMOFOX SET - 0803986

### Accessories

Label, highly flexible - MM-EMLF (EX12)R C1 BU/WH - 0803946



Highly flexible label, continuous, cassette, blue with white imprint, mounting type: adhesive, can be marked with THERMOFOX

---

Label, highly flexible - MM-EMLF (EX18)R C1 BU/WH - 0803947



Highly flexible label, continuous, cassette, blue with white imprint, mounting type: adhesive, can be marked with THERMOFOX

---

Label, highly flexible - MM-EMLF (EX24)R C1 BU/WH - 0803949



Highly flexible label, continuous, cassette, blue with white imprint, mounting type: adhesive, can be marked with THERMOFOX

---

Label, highly flexible - MM-EMLF (EX10)R C1 GN/WH - 0803950



Highly flexible label, continuous, cassette, green with white imprint, mounting type: adhesive, can be marked with THERMOFOX

---

Label, highly flexible - MM-EMLF (EX12)R C1 GN/WH - 0803952



Highly flexible label, continuous, cassette, green with white imprint, mounting type: adhesive, can be marked with THERMOFOX

---



## Thermal transfer printer set - THERMOFOX SET - 0803986

### Accessories

Label, highly flexible - MM-EMLF (EX12)R C1 RD/WH - 0803960



Highly flexible label, continuous, cassette, red with white imprint, mounting type: adhesive, can be marked with THERMOFOX

---

Label, highly flexible - MM-EMLF (EX18)R C1 RD/WH - 0803961



Highly flexible label, continuous, cassette, red with white imprint, mounting type: adhesive, can be marked with THERMOFOX

---

Label, highly flexible - MM-EMLF (EX24)R C1 RD/WH - 0803962



Highly flexible label, continuous, cassette, red with white imprint, mounting type: adhesive, can be marked with THERMOFOX

---

Insert label - MM-EMT (EX6)R C1 WH/BK - 0803963



Insert label, continuous, cassette, white with black imprint, mounting type: slide-in, can be marked with: THERMOFOX

---

Insert label - MM-EMT (EX8)R C1 WH/BK - 0803965



Insert label, continuous, cassette, white with black imprint, mounting type: slide-in, can be marked with: THERMOFOX

---

## Thermal transfer printer set - THERMOFOX SET - 0803986

### Accessories

Insert label - MM-EMT (EX15)R C1 WH/BK - 0803966



Insert label, continuous, cassette, white with black imprint, mounting type: slide-in, can be marked with: THERMOFOX

---

Insert label - MM-EMT (EX17)R C1 WH/BK - 0803967



Insert label, continuous, cassette, white with black imprint, mounting type: slide-in, can be marked with: THERMOFOX

---

Insert label - MM-EMT (EX18)R C1 WH/BK - 0803968



Insert label, continuous, cassette, white with black imprint, mounting type: slide-in, can be marked with: THERMOFOX

---

Insert label - MM-EMT (EX23)R C1 WH/BK - 0803969



Insert label, continuous, cassette, white with black imprint, mounting type: slide-in, can be marked with: THERMOFOX

---

Label - MM-EML (EX10)R C1 WH/BK - 0803970



Label, continuous, cassette, white with black imprint, mounting type: adhesive, can be marked with THERMOFOX

---

## Thermal transfer printer set - THERMOFOX SET - 0803986

### Accessories

Label - MM-EML (EX12)R C1 WH/BK - 0803971



Label, continuous, cassette, white with black imprint, mounting type: adhesive, can be marked with THERMOFOX

---

Label - MM-EML (EX18)R C1 WH/BK - 0803972



Label, continuous, cassette, white with black imprint, mounting type: adhesive, can be marked with THERMOFOX

---

Label - MM-EML (EX24)R C1 WH/BK - 0803973



Label, continuous, cassette, white with black imprint, mounting type: adhesive, can be marked with THERMOFOX

---

Label - MM-EML (EX10)R C1 SR/BK - 0803974



Label, continuous, cassette, silver with black imprint, mounting type: adhesive, can be marked with THERMOFOX

---

Label - MM-EML (EX12)R C1 SR/BK - 0803975



Label, continuous, cassette, silver with black imprint, mounting type: adhesive, can be marked with THERMOFOX

---

## Thermal transfer printer set - THERMOFOX SET - 0803986

### Accessories

Label - MM-EML (EX18)R C1 SR/BK - 0803976



Label, continuous, cassette, silver with black imprint, mounting type: adhesive, can be marked with THERMOFOX

---

Label - MM-EML (EX24)R C1 SR/BK - 0803978



Label, continuous, cassette, silver with black imprint, mounting type: adhesive, can be marked with THERMOFOX

---

### Printing system accessories

Case - THERMOFOX/CASE - 0805002



Hard-top case for storing the THERMOFOX printer and accessory parts

---

Case - THERMOFOX/BAG - 0805003



Shoulder bag for storing the THERMOFOX printer and accessory parts

---

Fastening clip - THERMOFOX/BELT CLIP - 0805004



Belt clip for fastening the THERMOFOX printer

---

## Thermal transfer printer set - THERMOFOX SET - 0803986

### Accessories

Mounting unit - THERMOFOX/MAGNET HOLDER - 0805008



Magnetic holder for mounting the THERMOFOX printer on metal surfaces, e.g., on the control cabinet

---

Battery - THERMOFOX/ACCU - 0805009



Rechargeable battery for operating the THERMOFOX printer

---

Power supply unit - THERMOFOX/ADAPTER - 0805010



Power supply unit for operating the THERMOFOX printer

---

Charging tray - THERMOFOX/CHARGER - 0805012



Charging tray, for charging the THERMOFOX/ACCU battery (0805009)

---

### Shrink sleeve

Shrink sleeve - MM-WMS 3,2 (EX5)R C1 WH/BK - 0803923



Shrink sleeve, continuous, cassette, white with black imprint, mounting type: slide-on, cable diameter: 1.0 - 3.2 mm, can be marked with THERMOFOX

---

## Thermal transfer printer set - THERMOFOX SET - 0803986

### Accessories

Shrink sleeve - MM-WMS 4,8 (EX9)R C1 WH/BK - 0803924



Shrink sleeve, continuous, cassette, white with black imprint, mounting type: slide-on, cable diameter: 1.6 - 4.8 mm, can be marked with THERMOFOX

---

Shrink sleeve - MM-WMS 6,4 (EX10)R C1 WH/BK - 0803925



Shrink sleeve, continuous, cassette, white with black imprint, mounting type: slide-on, cable diameter: 2.1 - 6.4 mm, can be marked with THERMOFOX

---

Shrink sleeve - MM-WMS 9,5 (EX16)R C1 WH/BK - 0803926



Shrink sleeve, continuous, cassette, white with black imprint, mounting type: slide-on, cable diameter: 3.2 - 9.5 mm, can be marked with THERMOFOX

---

Shrink sleeve - MM-WMS-2 3,2 (EX5)R C1 WH/BK - 0803927



Shrink sleeve, continuous, cassette, white with black imprint, mounting type: slide-on, cable diameter: 1.6 - 3.2 mm, can be marked with THERMOFOX

---

Shrink sleeve - MM-WMS-2 4,8 (EX9)R C1 WH/BK - 0803928



Shrink sleeve, continuous, cassette, white with black imprint, mounting type: slide-on, cable diameter: 2.4 - 4.8 mm, can be marked with THERMOFOX

---

## Thermal transfer printer set - THERMOFOX SET - 0803986

### Accessories

Shrink sleeve - MM-WMS-2 6,4 (EX10)R C1 WH/BK - 0803929



Shrink sleeve, continuous, cassette, white with black imprint, mounting type: slide-on, cable diameter: 3.2 - 6.4 mm, can be marked with THERMOFOX

---

Shrink sleeve - MM-WMS-2 9,5 (EX16)R C1 WH/BK - 0803930



Shrink sleeve, continuous, cassette, white with black imprint, mounting type: slide-on, cable diameter: 4.8 - 9.5 mm, can be marked with THERMOFOX

---

### Terminal marking

Label - MM-TML (EX4,2)R C1 TR/BK - 0803979



Label, continuous, cassette, transparent with black imprint, mounting type: adhesive, can be marked with THERMOFOX

---

Label - MM-TML (EX9,5)R C1 TR/BK - 0803981



Label, continuous, cassette, transparent with black imprint, mounting type: adhesive, can be marked with THERMOFOX

---

Label - MM-TMT (EX6,35)R C1 WH/BK - 0803982



Label, continuous, cassette, transparent with black imprint, mounting type: snap-on, can be marked with THERMOFOX

---

## Thermal transfer printer set - THERMOFOX SET - 0803986

### Accessories

Label - MM-TMT (EX9,5)R C1 WH/BK - 0803983



Label, continuous, cassette, white with black imprint, mounting type: snap-on, can be marked with THERMOFOX

---

Label - MM-TML (EX3,8)R C1 WH/BK - 1092026



Label, continuous, cassette, white with black imprint, mounting type: adhesive, can be marked with THERMOFOX

---

---