

# TOOLS

## PRECISION SCREWDRIVER SET

- 6 pc. flat blades 1.0, 1.2, 1.4, 1.8, 2.4, 3.0mm
- 3 pc. Phillips #00, #0, #1
- 1 Pick Up Tool and Pin Tip
- Molded Plastic case



No. JS7



## JEWELERS' SCREWDRIVER SET

No. JS6

Set of six screwdrivers with free-turning heads, precision made for jewelers, watchmakers, gauge makers, hobbyists etc.. Sizes are 1.0, 1.4, 2.0, 2.4, 3.0 and 3.5mm. Packed in clear plastic case.

## MINIATURE PRECISION NUTDRIVER SET

- 5 pc. nut driver
- 1/8", 9/64", 5/32", 11/32", 3/16"
- 1 piece cross bar



No. JS5

## PRECISION TWEEZERS 4-1/2"

These quality, stainless steel tweezers are excellent for electronic and fine assembly.

- No. 10132 - 4-1/2"
  - No. 10134 - Regular Fine Point 4-1/2"
  - No. 10136 - Curved Fine Point 4-1/2"
  - No. 10138 - Self Closing Fine Point 4-1/2"
  - No. 10140 - Self Closing 7"
  - No. 10130 - Kit of 4 Tweezers 4-1/2"
- (Nos. 10132, 10134, 10136 & 10138)



## Electronic FORCEPS Stainless Steel


These are fine, high-quality forceps, or surgical hemostats, which have become a standard in electronic service and assembly. Small parts can be handled easily, solder will not stick to these Stainless Steel tools. Serrated jaws provide a good gripping surface and all models have a locking feature when needed. Smaller size is intended for persons with smaller to average hand size.



Part no.	Size	Style
63-382	5-1/8"	Straight
63-384	5-1/8"	Curved
63-386	6-1/4"	Straight
63-388	6-1/4"	Curved

## 21 PIECE PRECISION SCREWDRIVER AND TOOL SET

This handy tool is great for repairs on all kinds of Electronic appliances and equipment. It is used by hobbyists and technicians alike. The set includes **Phillips sizes:** 3.0mm, 4.0mm, **Slotted Screwdriver size:** 1.0mm, 1.4mm, 2.0mm, 2.4mm, 3.0mm, 3.8mm, **Open wrench sizes:** 4.0mm, 4.5mm, 5.0mm, 6.0mm, **Hex key Wrench sizes:** 1.5mm, 2.0mm, **Nut Driver sizes:** 3.0mm, 3.5mm, 4.0mm, 4.5mm, 5.0mm all in a handy plastic case.



No. 63-12068 21 piece precision screwdriver & tool set

## 5 PIECE INSULATED - SCREW HOLDING SCREW DRIVER SET

This handy, quality screwdriver set gives user (5) fully insulated screwdrivers with added screw holding feature. Set is constructed of Chrome Vanadium Steel and includes #0, #1 and #2 straight blades and #1 and #2 phillips blade.



No. 63-315

## SNAP RING PLIER SET

This tool set comes complete with 4 sets of interchangeable jaws. It can be used for both internal and external snap ring retainer clips. The tool can be used with an effective range of 3/8" to 2" (10-50mm). There are jaws for 45°, 90°, 180°, Straight. The jaws are quickly and easily changed.



No. 63-8006 Snap Ring tool set

## STAINLESS STEEL PROFESSIONAL TOOLS

These finely machined stainless tools are durable and long-lasting. Extremely comfortable in user's hand. The cushioned handle grips provide very high insulation. All three tools are furnished with spring for ease-of-use. Philmore feels there is no finer value available today.



- No. SA703 - side cutter
- No. SA704 - needle point pliers
- No. SA705 - curved needle point pliers